Project / Job Name:

Location:

Fixture Type:

Notes:



S30112 - LED High Power Flashlight; 1800 Max Lumens; USB-C Rechargeable; 3.7 Volt; 10pc Tray Pack

GENERAL

Company	SATCO
EA Height	7.25
EA Width	3.75
EA Length	2.0
Material	Aluminum
Fixture Type	Rechargeable Search
Includes	USB-A to USB-C Charging Cable
Product Notes	Replaceable Rechargeable 3.6V Li-ion 21700 Battery; Charge Time: 5HRS
Status	Active
CCT Selectable	No
Wattage Selectable	No
Finish Family	Black
Additional Info	Ships in retail-ready display trays and packaging
Integrated Features	Replaceable Battery; Beam Adjustable
Lens Finish	Clear
Lens Material	Poly methyl methacrylate (PMMA)
Lensed	Yes
Portable Light Modes	High, Low, Medium, Strobe
Product Technology	LED
Serviceable Battery	No
Beam Distance (Ft)	1969
Battery Indicator	No
Digital Display	No
Drop Impact Rating	3.28 Ft (1M)
Battery Operating Temp	+32F to +104F (0C to +40C)
Light Source Quantity	Single
Power Bank Storage	4000mAh

ELECTRICAL

CCT (Kelvin Temp)	9000K
Dimmable	Yes-Dimmable
Color Temp	Daylight
CRI	50+
Dimming Type	Only dimmable via setting selection, Step Dimming
Operating Temp	+32F to +104F (0C to +40C)
Lumens	1800L/800L/150L
Volts	3.7V
Max Lumens	1800L
Connection	USB-C Rechargeable
Charge Time	5hr
Battery Chemistry	Lithium-ion (Li-ion)
Replaceable Battery Type	21700
USB Type In	1 USB-C

PHYSICAL

Finish	Black / Gray / Red
Housing Color	BlackGrayRed

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging
Portable Light Functions	Red Light Function, White Light Function

PACKAGING

UPC	045923300134
Case Cube	1.2991
Case Height	9.84
Case Length	12.2
Case Quantity	20
Case UPC	10045923300131
Case Weight	17.63
Case Width	18.7
EA Cube	0.0315
EA Height	7.25
EA Length	2.0
EA Quantity	1
EA Weight	0.64
EA Width	3.75
Inner Cube	0.4474
Inner Height	8.43
Inner Length	10.79
Inner Quantity	10
Inner UPC	20045923300138
Inner Weight	7.93
Inner Width	8.5
Pack Type	Color Box
Web Height	6.22
Web Length	1.69
Web Width	1.69

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IPX4
ROHS Compliant	Yes
Energy Star Certified	No
T24/JA8 Compliant	No
Performance Standards	ANSI PLATO FL1

© Satco Products, Inc.
All rights reserved 2026