Stock Code: **62542LEDD-CH/OPL**

Collection: Madison

PRODUCT INFORMATION

Base: 62542
Parent: 62542LEDD
Mounting Type: Wall
UPC: 641594234879
Finish: Chrome
Diffuser: Opal

PRODUCT MEASUREMENTS

FIXTURE

Length:
Width: 39.25"
Diameter
Height: 4.5"
Extension: 3.25"
Overall Height:

BACKPLATE / CANOPY

Length
Width:
Diameter: 4.5"
Height:

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Steel
Diffuser Material: Glass
Lamping Type: SSL (Dedicated LED)
Jbox: Standard
Lamping Base: SSL
Lamp Wattage: 32 W
Lamp Quantity: 1
Total Wattage: 32 W
Voltage: 120v
Lamps Included: Yes

QUALIFICATIONS

Location Rating Damp
Certifitcation: ETL (US/Canada) Listed
ADA Compliant: Yes
Energy Star: No
JA8 Compliant: Yes
Emergency Lighting: No
Marine Grade: No
Warranty: 5 Year

PHOTOMETRICS

Dimmable: Yes
Nominial Lumens 2560 Lm
CRI: 90
Delivered Lumens: 2226 Lm
CCT: 3000K
Recommended Dimmers:
(TRIAC)LUTRON Diva DVCL-153P; (TRIAC)LUTRON Skylark CL SCL-153 or SCL-153P; (ELV)LEGRAND Touch ADTH700RMTUM1; (ELV)LUTRON Diva DVELV-300P; (ELV)LUTRON Maestro CL MACL-153M

Additional Notes:
Horizontal and Vertical Mounting; Optional Color Tempature 100 Piece Minimum Order Quantity; Custom Finish 100 Piece Minimum Order Quantity

Project Name: _____
Location: _____
Type: _____
Quantity: _____
Notes:

LINE DRAWING



IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____