Counter bearing
EAMG-U1-110

Part number: 1354284



Data sheet

Feature	Value
Size	110
Type code	EAMG
Mounting position	Any
Max. rotational speed	5000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Product weight	169 g
Note on materials	RoHS-compliant