Branching module
PMBL-90-HP3

Part number: 1401366

Data sheet

Feature	Value
Size	90
Nominal width DN	36
Type code	PMBL
Series	L
Mounting position	Any
Structural design	Branching module
Symbol	00991510
Operating pressure	0 MPa ... 5 MPa
Operating pressure	0 bar ... 50 bar
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Operating medium	Compressed air as per ISO 8573-1:2010 [-:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS conformity	VDMA24364 zone III
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	2000 g
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Wrought aluminum alloy