Quick coupling
EAMD-28-22-14-10X12

Part number: 1453861

Data sheet

Feature	Value
Diameter of holder 1	14 mm
Diameter of holder 2	10 mm
Size	28
Nominal length	22 mm
Type code	EAMD
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	3.5 kgmm²
Transferable torque	9 Nm
Product weight	43 g
Note on materials	RoHS-compliant