



jalas® EXALTER 9998 GTX

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRC, WR, HRO

Learn more

A GORE-TEX BOOT FOR MEDIUM COLD WINTERS

A waterproof safety boot with GORE-TEX, ideal for a wet and medium cold season. Uppers in highly protective full grain leather and functional textile for support and protection. Medium cold insulation lining keeps feet warm and comfortable. BOA® and high grip Vibram® Nitril rubber outsole. aluminium toe cap and soft textile nail protection insert.

CHARACTERISTICS

- High level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- GORE-TEX Performance Comfort Footwear technology
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Ventilating insole
- BOA® Fit System
- Quick-tie
- Stabilizator
- Waterproof
- Ergonomically shaped
- Soft
- Specially designed details
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Sprain injuries, Antistatic, Wet feet

PRIMARY ENVIRONMENTS OF USE

Outdoors, All-year use, Environments with risk for outsole penetration, Wet environments, Moist environments, Dirty environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION Exalter
UPPER MATERIAL Full-grain leather, Microfiber, Textile
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyamide
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.56 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC TP TC 019:2011

EN ISO 20345:2011
S3, SRC, WR, HRO

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile
- Stabilizator
- Heat-resistant outsole
- Waterproof

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
34	1.5	2.5	3.5	9998-34	6408487534898
35	2	3.5	4	9998-35	6408487534935
36	3	4	5	9998-36	6408487534973
37	4	5	6	9998-37	6408487535017
38	5	5.5	6.5	9998-38	6408487535055
39	6	6.5	7.5	9998-39	6408487535093
40	6.5	7.5	8.5	9998-40	6408487535130
41	7	8	9	9998-41	6408487535178
42	8	9	10	9998-42	6408487535215
43	9	9.5	11	9998-43	6408487535253
44	10	10.5	11.5	9998-44	6408487535291
45	10.5	11	12.5	9998-45	6408487535338
46	11	12	13	9998-46	6408487535376
47	12	13	14	9998-47	6408487535413

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.