




EAN:	4013288221841	Size:	165x70x35 mm
Part number:	05004282001	Weight:	258 g
Article number:	8009 Zyklop Pocket Set Imperial 1	Country of origin:	CZ
		Customs tariff number:	82041100

- Compact Zyklop ratchet with integrated bit magazine
- The magnetic direct mounting simultaneously turns the 3/8" ratchet into a bit ratchet screwdriver with 1/4" bit mounting
- Freely pivoting ratchet head with 5 predefined locking positions
- Fine tooth reversible ratchet (72 teeth) for a low return angle of only 5°
- Captive and freely swivelling bit magazine for easy removal and secure storage of the bits

Compact Zyklop ratchet with bit magazine for the pocket. Magnetic direct mounting for 1/4" bits and 3/8" sockets. Rapid tool change thanks to the non-locking mounting. As the head is lockable at 0°, 15° and 90°, the tool can be used as a ratchet and as a ratchet screwdriver. The fine toothing with 72 teeth allows for a low return angle of 5°. Wide range of applications thanks to 12 bits integrated in the handle. The robust ratchet mechanism allows for ample torque. Perfect combination of a Zyklop ratchet with a 12-piece screwdriver set.



Web link

<https://www.wera.de/en/05004282001>

Wera - 8009 Zyklop Pocket Set Imperial 1
05004282001 - 4013288221841

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Combination tool mounting




Compact Zyklus ratchet with integrated bit magazine



The magnetic direct mounting is suitable for 3/8" sockets as well as 1/4" bits without the need for an adapter.

With integrated bit magazine




A captive, freely swivelling bit magazine for 12 bits (1/4", 25 mm length) is integrated in the handle of the compact Zyklus ratchet.

Swivelling bit magazine



The swivelling bit magazine allows for the bits to be removed easily in almost any situation and cannot be lost. The bits are safely stored.

Freely pivoting ratchet head




The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Locking the ratchet head



Thanks to the sliding switch on both sides, the ratchet head can be locked at the pre-defined positions 0° as well as 15° and 90° to the right and left.

Small return angle



The fine tothing with 72 teeth allows for a low return angle of only 5° for working in constricted screwdriving situations.

Simple direction change



The Zyklus Pocket ratchet can be quickly and easily reversed for clockwise/anti-clockwise rotation in any position using the knurl.

Web link

<https://www.wera.de/en/05004282001>

Wera - 8009 Zyklus Pocket Set Imperial 1
05004282001 - 4013288221841

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

8009 Zyklus Pocket, 3/8" x 1/4" x 133 mm



1x 3/8" x 1/4" x 133 mm



851/1 BTZ bits, PH 1 x 25 mm



05056420001
05056422001

1x PH 1 x 25 mm
1x PH 2 x 25 mm



867/1 BTZ TORX® bits, TX 10 x 25 mm



05066120001
05066122001
05066124001
05066126001

1x TX 10 x 25 mm
1x TX 15 x 25 mm
1x TX 20 x 25 mm
1x TX 25 x 25 mm



840/1 Z bits, 1/8" x 25 mm



05135073001
05135074001
05135075001
05135076001

1x 1/8" x 25 mm
1x 5/32" x 25 mm
1x 3/16" x 25 mm
1x 1/4" x 25 mm



868/1 Z Square-Plus bits, # 1 x 25 mm



05066405001
05066410001

1x # 1 x 25 mm
1x # 2 x 25 mm



Web link

<https://www.wera.de/en/05004282001>

Wera - 8009 Zyklus Pocket Set Imperial 1
05004282001 - 4013288221841

Wera Werkzeuge GmbH
Korzer Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de