Connecting cable
KRP-1-24-2,5

Part number: 165612

Data sheet

Feature	Value
Type code	KRP
Type of mounting	With through-hole
Mounting position	Any
Product weight	49 g
Electrical connection	2-pin Socket, angled
DC operating voltage range	≤26 V
Operating voltage range AC	≤20 V
Current rating	1 A
Cable length	2.5 m
Cable diameter	3.5 mm
Cable design	2 x 0.25 mm²
Degree of protection	IP65
Ambient temperature	-10 °C ... 50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Material of cable sheath	PVC
Housing material	PUR
Material of pin contacts	Bronze