




Brass Pop-Up Installation Instructions







NOTICE

Failure to follow all directions may cause leaks
which may result in water damage

www.kingstonbrass.com


TOLL-FREE CUSTOMER SERVICE: 1-877-2-KBRASS
TECHNICAL SUPPORT E-mail: service@kingstonbrass.com
12775 Reservoir Street, Chino, CA 91710


Tools Required

				
Basin Wrench	Adjustable Wrench	Teflon Tape	Silicone Sealant	Screwdriver

INSTALLATION:

1. Remove the flange (2), plug (1) from the drain body (7).
2. Turn the lock nut (6) downwardly to the lower position of drain body (7). Push washer (4)/ (5) and rubber gasket (3) down.
3. Insert drain body (7) upwardly with (3)/(4)/(5)/(6) parts and tailpiece(13) through the drain hole from the underside of sink. Position the side hole of drain body (7) toward the rear wall.
4. Apply a small bead of silicone caulking (Do not use plumbers putty) under drain flange (2), then thread the flange (2) on to the top of the drain body (7) until it can be fixed firmly on the bottom of sink.
5. Move up rubber gasket (3), washer (4)/(5) and tighten up the locknut (6) with a wrench until the rubber gasket (3) can completely and tightly seal the drain hole beneath the sink.
6. Insert the plug (1) into the flange (2). Make sure its bottom hole is aligning with the side hole of drain body (7).
7. Remove the nut from the side hole of drain body. Remove clip (12) and two plastic bushings from the ball rod (8).
8. Place one plastic bushing in the side hole with its concave surface face out. Insert the short side of ball rod from the side hole and through the bottom hole of plug (1). Put the other plastic bushing and nut on the long side of ball rod. Make sure the concave surface of bushing face to the ball. Tighten up the nut by hand.
9. Move the ball rod (8) up and down to test the plug (1) can open and close smoothly.
10. Connect pop-up rod (9) and ball rod (8) with lift rod strap (11). Try and test the proper connection position and fix them by clip (12) and set screw (10) tightening. .
11. Pull up the pop-up rod (9) to the closed position of the plug (1), then turn on the faucets to fully fill the sink with water. Examine and ensure that no water is leaking from the drain body.
12. Push down the pop-up rod (9) to the open position of plug (1) to drain water. Examine to make sure no water leakage around the rubber gasket (3) or side hole of drain body. If leakage found, adjust the rubber gasket (3), re-tighten up the lock nut (6) or the nut on side hole until no more leakage found.



	PROBLEM
	On my faucet drain, the horizontal rod on the drain does not reach the adjustment bar that comes down vertically, what can I do ?
	CORRECTIVE ACTION
	Try bending the adjustment plate that comes down (11) from the pop-up rod, first move the plate as far down as possible then gently bend towards the drain at 45 degree angle, then another 45 degree angle bend down to facilitate the insertion of the horizontal pivot rod, in most cases this procedure will help you reach the horizontal pivot rod.