KRUD KUTTER®
HOUSE WASH

DESCRIPTION AND USES

Krud Kutter® House Wash Wash is a proprietary formulation which contains a unique additive which removes tough stains from mildew, mold, algae, fungus and moss, and leaves the surface completely clean. In addition, special surfactants penetrate the surface to safely and easily dissolve the toughest stains from dirt, oil, grease, bird droppings, tree sap, and acid rain. Even removes gray weathering on wood, chalking and oxidation.

Krud Kutter House Wash is safe and effective on most surfaces. Recommended for exterior siding (wood, vinyl, aluminum), roofing of all types (asphalt shingles, fiberglass shingles, cedar, tile), gutters, stucco, brick and cement block, masonry, walkways and walls.

PRODUCTS

SKU	DESCRIPTION
HW32H4	32 oz. Hose End
HW56H4	56 oz. Hose End
HW012	1 Gallon Bottle
HW05	5 Gallon Pail

PRODUCT APPLICATION

DIRECTIONS

IMPORTANT – READ ENTIRE LABEL BEFORE USE

- When using a pressure washer to clean painted surfaces, please be aware that water pressure alone may remove paint, or highlight existing discoloration caused by the sun's UV rays.
- From the garden hose, rinse any nearby plants with clean water.
- Always test on an inconspicuous area first.
- Any overspray can be neutralized with large volumes of water.
- On extremely soiled or mildewed surfaces it may be necessary to scrub with a bristle brush, and a second application may be needed. Mildew may not be completely removed from porous surfaces.
- For best results when cleaning decks, apply by pump-up garden sprayer, leave for 5 to 10 minutes, and rinse off with water.
- For heavy oil and grease stains (such as on driveways and garage floors), pour product directly onto the stain. Allow to penetrate for 10 minutes; then follow normal application procedures.
- In case of severe oil and grease stains on porous surfaces, oil may bleed to the surface or leave a residual stain. Repeat applications may lighten stains, but not remove completely.
- Do not mix this product with any other chemicals.

PRODUCT APPLICATION (cont.)

DIRECTIONS FOR HOSE END SPRAYER:

For best results use on a wet surface. Attach garden hose to back of sprayer with valve in "OFF" position. Turn on water to the hose. With valve in "RINSE" position and wet the surface to be cleaned. With valve in "CLEAN" position, apply the cleaner to the surface from the top down. Allow to work for 5-10 minutes. Do not allow to dry on surface.

Rinse off treated surface with valve in "RINSE" position. Turn hose on full pressure for best results. Rinse surrounding areas and vegetation with water. On extremely soiled or mildewed surfaces, it may be necessary to scrub with a bristle brush, and a second application may be needed.

DIRECTIONS: PRESSURE WASHER APPLICATION:

Contains anti-corrosive agents to safeguard pressure washer parts (bleach can erode O-rings). Rinse surrounding plants with water, before and after application.

Place detergent application siphon tube and screen filter directly into container. Open meter valve (if applicable) for maximum product flow. For reservoir machines, pour the product (full strength) into pressure washer. Spray at low pressure onto a wet surface. On vertical surfaces, always spray from the top down. Allow product to remain on the surface for 5 to 10 minutes to penetrate. Do not allow product to dry on surface. Remove siphon tube from solution and rinse surface with high-pressure spray thoroughly. Flush siphon tube with clean water prior to storage. Spray until thoroughly wet. Treated surface must remain wet for 10 minutes before wiping. For heavily soiled areas a pre-cleaning step is required. The pre-clean step must be done according to the instructions under Kitchen/Bathroom/ Household Cleaning. Rinse with potable water after use on surfaces that come in contact with food.

NO BLEACH OR AMMONIA

CAUTION! EYE AND SKIN IRRITANT. This product contains alkaline detergents. Do not take internally. In case of contact with eyes or skin, flush with water for at least 15 minutes. If irritation persists, seek medical attention. If swallowed, take large amounts of water. **Do not induce vomiting.** Get medical attention.

KEEP OUT OF REACH OF CHILDREN.

	TECHNICAL DATA	KRK-03

KRUD KUTTER®
HOUSE WASH

PHYSICAL PROPERTIES

	HOUSE WASH
Composition	Proprietary Ingredients in a Water-based Solution
Color	Clear
pH	<12
VOC	0%
Practical Coverage	32 ounces – 800-1,000 square feet
	56 ounces – 1,600-2,000 square feet
	1-Gallon – 3,200-4,000 square feet
	5-Gallons - 16,000-20,000 square feet
Shelf Life	NA
Flash Point	Non-flammable
Caution!	**EYE AND SKIN IRRITANT.** This product contains alkaline detergents. Do not take internally. In case of contact with eyes or skin, flush with water for at least 15 minutes. If irritation persists, seek medical attention. If swallowed, take large amounts of water. **Do not induce vomiting.** Get medical attention. **Do not induce vomiting.** Get medical attention. **KEEP OUT OF REACH OF CHILDREN**.
Safety Information	For additional information, see SDS

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.