



### PIP® Traverse™

Vented, Industrial Climbing Helmet, Type II, Non-MIPS, ABS Shell, EPS Liner, HDPE Suspension, Wheel Ratchet Adjustment, with 4-Point Chin Strap

- Ultra-lightweight vented shell made with ABS material provides superior protection while promoting air circulation
- EPS foam impact liner helps absorb the forces of top-of-head, front, side, and rear impacts
- Includes an adjustable 4-point cross-over chin strap with quick release buckle for a safe and secure fit
- Rugged SURE-LOCK adjustable wheel ratchet ensures proper suspension performance and fit for all head sizes
- Inner suspension includes comfortable padding for above the brow line
- Meets ANSI Z89.1-2014 Type II, Class C

## Technical Data

|                      |                                                                          |
|----------------------|--------------------------------------------------------------------------|
| Color                | Gray, Dark Green, Red, Black, White, Orange, Yellow, Navy, Hi-Vis Yellow |
| Sizes Available      | OS                                                                       |
| Packaging            | Boxed                                                                    |
| Packed               | 18/Case                                                                  |
| Case Dimensions (in) | 28.35 x 11.61 x 30.71                                                    |
| Case Weight (lbs)    | 29.17                                                                    |
| Country of Origin    | China                                                                    |
| Shell Material       | ABS                                                                      |
| Shell                | Vented                                                                   |
| Brim Style           | Cap Style                                                                |
| Brim Length          | Micro                                                                    |
| Size Adjustment      | Wheel Ratchet                                                            |
| Suspension           | Foam Cradle System                                                       |
| Chin Strap           | 4-Point Polyester                                                        |
| Sweatband            | Polyester EVA                                                            |
| Size Range           | 53cm-63cm                                                                |
| Construction         | Standard - Without MIPS                                                  |
| Certifications       | ANSI/ISEA Z89.1, EN 12492                                                |

## Performance Data

|                  |         |
|------------------|---------|
| ANSI Type        | Type II |
| Electrical Class | Class C |

## Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

## SKU Information

| SKU             | COLOR         | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|-----------------|---------------|------|--------------|----------------|----------------|
| 280-HP1491RV-11 | Black         | OS   | 616314960215 | 10616314960212 | 20616314960219 |
| 280-HP1491RV-04 | Dark Green    | OS   | 616314960499 | 10616314960496 | 20616314960493 |
| 280-HP1491RV-09 | Gray          | OS   | 616314960451 | 10616314960458 | 20616314960455 |
| 280-HP1491RV-44 | Hi-Vis Yellow | OS   | 616314960253 | 10616314960250 | 20616314960257 |
| 280-HP1491RV-08 | Navy          | OS   | 616314960291 | 10616314960298 | 20616314960295 |
| 280-HP1491RV-03 | Orange        | OS   | 616314960536 | 10616314960533 | 20616314960530 |
| 280-HP1491RV-15 | Red           | OS   | 616314960338 | 10616314960335 | 20616314960332 |
| 280-HP1491RV-01 | White         | OS   | 616314960376 | 10616314960373 | 20616314960370 |
| 280-HP1491RV-02 | Yellow        | OS   | 616314960413 | 10616314960410 | 20616314960417 |