



MCR
SAFETY

Rubicon (T4)

Safety Glasses

Premium Series Specification Sheet

PRODUCT DESCRIPTION:

The Rubicon® T4 series curved frameless lens design offers a close orbital seal for increased protection, a soft gel nose piece for added comfort, and durable metal temples with non-slip, soft temple material. The frameless design keeps your line of vision clear helping you focus on the task at hand. The UV-AF® Anti-Fog coated lens are Eco-friendly and UV cured, providing 3 times greater Anti-Fog performance than generic Anti-Fog safety glasses. These high quality safety glasses have a lifetime frame warranty and are engineered to provide the highest level of innovation for consumers that demand the very best. Choose the best safety glasses, choose MCR Safety!



To learn more about our anti-fog styles and anti-fog coating options click [here!](#)

FEATURES:

- Curved frameless lens design offering close orbital seal
- Resilient spring hinge temples
- UV-AF® Anti-Fog Lens
- Comfortable TPR Nose Piece
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays

TECHNICAL DATA FOR: T4110AF

Series	Rubicon (T4)	ANSI Z87+	Yes
Category	Safety Glasses	CE EN166	Yes
Scratch Resistant	Yes		
Packaging	Multicolor Gravity Feed		
Case Pack	144	Case Weight	15.516 lb.
Case Dimensions	20.079 x 19.291 x 10.630	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
T4110AF	Clear	UV-AF Anti-Fog	Yes	90	N/A	Metal	Black

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

Rubicon (T4)

Safety Glasses

Premium Series

Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
T4112AF	Gray	UV-AF Anti-Fog	Yes	13	N/A	Metal	Black
T4113AF	Light Blue	UV-AF Anti-Fog	Yes	68	N/A	Metal	Black
T411G	Emerald Mirror	Duramass Hard Coat	Yes	13	N/A	Metal	Black
T411R	Fire Mirror	Duramass Hard Coat	Yes	13	N/A	Metal	Black

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved