Spiral plastic tubing
PUN-10X1,5-SG-2,4-BL-1/4

Part number: 533463

Data sheet

Feature	Value
Working length	2.4 m
Outside diameter	9.5 mm
Block length	0.889 m
Bending radius relevant for flow rate	50 mm
Inside diameter	6.4 mm
Winding diameter	42 mm
Number of windings	21
Type code	PUN-SG
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 60 °C
Nominal tightening torque	11 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	180 g
Pneumatic connection 1	External thread G1/4
Pneumatic connection 2	External thread G1/4
Color	Blue
Shore hardness	A 87 +/-3
Material of connecting thread	Brass Nickel-plated
Note on materials	Free of copper and PTFE
Antikink device material	POM
Material of pneumatic tubing	TPE-U(PU)