

COMBO L-BAR SEALER & SHRINK TUNNEL

MODEL SS-1519ECMC-Series

sealersales



Economical for low to medium production

- Features Micro Knife technology
- Capable of 8-12 packages/minute
- Seal size: 15"W x 19"L
- Tunnel features re-circulating air chamber
- Recommended film: POF 60-80G (no PVC)



The **SS-1519ECMC-Series** Semi-Automatic L-Bar Sealer with Shrink Tunnel is an economical machine designed for low to medium production of 8-12 packages per minute. With its heavy duty frame construction, cast aluminum seal head and Micro Knife seal technology, you will get years of use with minimal repairs. The attached shrink tunnel features a live roller rod conveyor with fully re-circulating air chamber, AC variable speed conveyor, 0-60 feet/minute speed, digital temperature control and automatic cool down and shut off. We recommend this combo unit for polyolefin film with 60-80G thickness.

This series provides a range of choices to fulfill your sealing requirements.

- Voltage: 110V or 220V (We highly recommend 220V for a more efficient shrink tunnel.)
- Tunnel height: 6" or 8" (220V only)
- L-Bar magnet hold which will release seal bars automatically after seal is complete (SS-1519ECM)
- L-Bar magnet hold and power discharge conveyor to automatically bring product to tunnel (SS-1519ECMC)

SPECIFICATIONS	SS-1519EC*	SS-1519ECM*	SS-1519ECMC
		MAGNET HOLD	MAGNET HOLD POWER DISCHARGE CONVEYOR
POWER	110V / 1PHASE /20 AMPS <u>OR</u> 220V / 1 PHASE / 15 AMPS		
SEAL DIMENSIONS	15"W x 19"L		
TUNNEL DIMENSIONS	20"L x 16"W x 6"H (OPTION: 8"H)		
MACHINE DIMENSIONS	76"L x 26"W x 50"H		
MAX FILM WIDTH	22"		
PRODUCTION RATE	8-12 PPM		
WEIGHT	460-LBS		

**via special order*

COMBO L-BAR SEALER & SHRINK TUNNEL

MODEL SS-1519ECMC-Series

sealersales



Tunnel Control Panel



Shown with:

Optional SS-180-24
Gravity Curved Conveyor



Sealer Control Panel



Tunnel Features

- Fully re-circulating air chamber
- AC variable speed drive; 0-60FPM
- Live roller rod conveyor
- Automatic cool down w/ shut-off
- Digital temperature controller 0-400°F
- Anti-jam safety feature on conveyor



Micro Knife Technology

- Single piece of PTFE band ribbon with round corner seals - reduces dog ears
- Will seal polyolefin shrink film
- 1 year warranty on band ribbon
- Dual magnet hold down (SS-1519ECM)
- Dual magnet and power discharge conveyor (SS-1519ECMC)



Pin Wheel Hole Punch

- Easy load film rack
- Multiple pin wheels provide air evacuation
- Adjustable product loading tray