



Technical Data



Bouton® Optical Eva®

Rimless Safety Glasses with Clear / Pink Temple, Pink Lens and Anti-Scratch Coating

Color	Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 10.24 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Malaysia
Lens	Tinted
Frame Style	Rimless
Lens Color	Pink
Frame Fit	Narrow Face
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Rubber Tips
Base Curve	10
Construction	Womans Fit
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

- Smaller and more narrow than standard safety glasses
- Eva's construction allows the eyewear to better fit the facial structure of a woman
- Provides a more secure fit on the nose
- Lightweight, rimless design provides all day user comfort
- Pink rubber co-molded temples provide a secure fit
- Molded nose bridge design to fit the vast majority of users
- 10 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Construction Applications
- Public Works

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-10

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-10-0900	Pink	Clear	Clear	AS	616314055621	01616314055620	02616314055629
250-10-0904	Pink	Tinted	Pink	AS	616314055645	01616314055644	02616314055643
250-10-0920	Pink	Clear	Clear	AS/AF	616314055638	01616314055637	02616314055636
250-10-5501	Pink	Tinted	Gray	AS	616314056000	01616314056009	02616314056008
250-100-0018	Brown				198987100315	10198987100312	20198987100319
250-100-0020	Clear				198987100346	10198987100343	20198987100340
250-100-0021	Smoke				198987100339	10198987100336	20198987100333
250-100-0029	Amber				198987022747	10198987022744	20198987022741

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated