BESALIGHTING

# JILLY

VANITIES WALL

location:
**DAMP**

## SPECIFICATIONS:

### DESCRIPTION
1-3 light vanity luminaires featuring handcrafted glass shade(s).

### LAMPING
**Standard:** 60W Medium-based 120V, lamp not included. Dimmable with standard incandescent dimmer (not included).
**EDI:** 40W Edison Filament Medium-based, 120V, lamp included.
**LED Filament:** 5W Replaceable LED Filament lamp, 120V, dimmable, 90+ CRI, 2200°**K** CCT, 450 lumens, 15,000 hours, lamp included.

### DIFFUSER
Shade shall be handcrafted glass of various decors. 6.5" Dia. x 6." H.

### CONSTRUCTION
Backplate and Bar are plated steel.

### METAL FINISH
Fixture shall be finished in Bronze or Satin Nickel.

### MOUNTING
Installs directly to a 4" octagonal outlet box. Wall-mount only.

### LABELS
UL or ETL Listed. Suitable for Damp Locations (interior use only).

VAPOR CLEAR

JILLYAM
VAPOR AMBER



JILLYSM
VAPOR SMOKE



**For ordering information, see next page**

All dimensions provided are nominal.
Allowance must be made for dimensional tolerance in handcrafted glasses.

**REV 12/18**

## ORDERING:

| FIXTURE | GLASS OPTIONS | LAMP OPTIONS | METAL FINISH |
|---|---|---|---|
| **1WC** 1 Lt. Sconce 6.5″ L | **JILLYAM** Vapor Amber | **(blank)** 60W T10 Incan | **BR** Bronze |
| **2WC** 2 Lt. Vanity 15″ L | **JILLYCL** Vapor Clear | **EDI** 40W Edison | **SN** Satin Nickel |
| **3WC** 3 Lt. Vanity 25.25″ L | **JILLYSM** Vapor Smoke | **EDIL** 5W LED Filament | |

**Ex. 2WC-JILLYCL-SN**
Vapor Vanity, Vapor Clear Shade,
Satin Nickel Finish




1WC: 6.5″ L

2WC: 16″ L

3WC: 25″ L



**Project Information:**