SKU # H10-LED-G2-KIT

Part # 1002626

Description

G2 H10 5500K TRUE LED Headlight Kit

Categories HID & LED Headlights, LED Headlight Conversions

Sub-Categories LED Conversion Kits, Gen2 LED Headlight Kits

UPC 812867023180

Unit of Measure Kit

Related Skus:
RELAY-RES, RELAY-CAP

Cross Sell Skus:

Condition
New

Manufacturer
Race Sport Lighting

EZ Category
Gen2 LED Headlight Kit

Harmonization Code
8512.20.2080

Universal
YES

Life Expectancy

SEMA Product
Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity
Headlight Conversion Kit

Operating Voltage
9-24VDC

Current Draw
3A

Wattage
35-Watts

Chip Type

IP Rating
IP67

LUX
2,600 LUX

Kelvin (ColorTemperature)
5,500K

Universal or Vehicle Specific
Universal

Made In
China

Warranty
No Warranty

Lumens
3,200lm

Beam Pattern
N/A

Product Information

The Next Generation in LED Headlight Technology Race Sport Lighting's LED Headlight Kit stomps the competition with over 3000 Lumens of output and an low 3 Amp current draw. Generation 2 goes the extra mile with an more focused beam pattern for brighter more controlled light output, wide input voltage range for a variety of vehicles and aluminum thermal core technology to maintain cooler operating temperatures. Easy to install kit comes with two-Year Warranty, 2 LED headlights, 2 built-in fans and 2 drivers. Priced per kit. • Improved cooling design • 2-3 times further vision than standard halogen bulbs • Instant On Technology provides full power light immediately • 5500 Kelvin • 35W operating power • Operating voltage range: 9V-24V • 3000 Lumen (2600lux)- 30% more luminous than Gen 1 Kits • 2 Year Warranty

Est. Labor	Hours		
Gross Weight	1.20	Width	8.00
Net Weight	1.20	Height	2.50
DIM Weight	1.15	Depth	8.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov