EPSON
EXCEED YOUR VISION

SPECIFICATION SHEET

Scanners

Flatbed with ADF

DS-1630
Flatbed Color Document Scanner



The affordable, versatile flatbed scanner with ADF for more productivity.

Versatile scanning from a leader in image capturing technology — auto-duplex scanning through the Auto Document Feeder (ADF), plus a flatbed for photo IDs, passports, fragile items and more

Scan stacks of documents up to 25 ppm[1] — features a 50-page ADF

Seamless compatibility with document management systems — includes TWAIN and ISIS® drivers for easy integration with existing software

Scan to online storage accounts[2] — intuitively scan to Dropbox®, SharePoint®, Evernote®, FileBound and Google Drive™ with Epson® Document Capture software

Organize easily with the included software — also features ABBYY® FineReader®

Streamline your workflow — easy, one-touch scanning to folders, email, online storage accounts[2] and more

Scan originals in a variety of sizes — up to 8.5" x 11.7" on the flatbed and up to 8.5" x 14" using the ADF

Generate searchable and editable files — scan to editable Word and Excel® files[3] or searchable PDF files; OCR software included

Intelligent color and image adjustments — auto crop, skew correction, blank page and background removal with Epson Image Processing Technology

EPSON
EXCEED YOUR VISION

DS-1630 Flatbed Color Document Scanner

Specifications

Type Flatbed color document scanner
Sensor Type Contact Image Sensor (CIS)
Optical Resolution Flatbed: 1200 dpi; ADF: 600 dpi
Light Source 3-color RGB LED
Hardware Resolution
Flatbed: 1200 x 1200 dpi; ADF: 600 x 600 dpi
Scanning Speed[1] 25 ppm simplex, 10 ipm duplex (300 dpi, Black-and-White, Grayscale, Color)
Color Scan Mode (Bit Depth) RGB x 30-bit internal/24-bit external
Grayscale Scan Mode (Bit Depth) 8-bit internal/external
Buttons Power, Scan, Stop
Automatic Document Feeder
Capacity: 50 sheets
Document size: Max.: 8.5" x 11.7" duplex/simplex, 8.5" x 14" simplex; Min.: 3.5" x 6.7" duplex, 3.5" x 5" simplex; Long paper: 8.5" x 120" simplex
Paper weight: 50 to 120 g/m²
Flatbed
Document Size: 8.5" x 11.7"
Connectivity SuperSpeed USB 3.0, optional Network Interface Unit (RJ-45, 10BaseT/100BaseTX)
Daily Duty Cycle 1,500 sheets

System Requirements

Windows® 10, Windows 8/8.1, Windows 7
Mac OS® X 10.6.8 – 10.11.x
Software requires Internet connection for download and installation

General

Environmental Conditions
Temperature (operating): 50 ° to 95 °F (10 ° to 35 °C)
Humidity: 20 – 80% (no condensation)
Power Requirements Voltage: AC 100 – 240 V
Power Consumption
Operating: 11 W
Ready: 5.8 W
Sleep: 0.8 W
Off: 0.15 W
Warranty 1-year Advance Exchange limited warranty in the U.S. and Canada
Support The Epson Connection℠, Pre-sales support U.S. and Canada 800-463-7766
Country of Origin Indonesia
Dimensions (W x D x H) and Weight
Product only: 12.5" x 11.7" x 4.8", 9 lb

Software Included

Epson Scan, Document Capture Software, ABBYY FineReader OCR, (software requires Internet connection for download and installation)
Driver Support TWAIN, ISIS

What's in the Box

DS-1630 Scanner, Start Here poster, SuperSpeed USB cable, power cable, warranty sheet

Eco Features

RoHS compliant
Recyclable product[3]
Epson America, Inc. is a SmartWay® Transport Partner[4]
ENERGY STAR® qualified
Mercury-free, LED light source — lower energy consumption than a fluorescent lamp

Ordering Information

DS-1630 Scanner	B11B239201
Network Interface Unit	B12B808441
1-year Extended Service Plan	EPPMSCANEX1



Network scanning requires optional Network Interface Unit

1 Based on letter-sized scans at 300 dpi in Black-and-White, Grayscale or Color Mode. | **2** With Epson Document Capture software installed on the connected Windows PC or Mac®. | **3** For convenient and reasonable recycling options, visit www.epson.com/recycle | **4** SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.

See the latest innovations from Epson Business Solutions at **www.epson.com/forbusiness**

Better Products for a Better Future™
eco.epson.com

SmartWay Transport Partner
Getting There With Cleaner Air

ENERGY STAR

Contact:

Epson America, Inc.
3840 Kilroy Airport Way, Long Beach, CA 90806

Epson Canada Limited
185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com
www.epson.ca

Specifications and terms are subject to change without notice. EPSON is a registered trademark, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future is a trademark of Seiko Epson Corporation. Epson Connection is a service mark of Epson America, Inc. Mac, Mac OS and OS X are trademarks of Apple Inc., registered in the U.S. and other countries. Google Drive is a trademark of Google Inc. SmartWay is a registered trademark of the U.S. Environmental Protection Agency. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2016 Epson America, Inc. Com-SS-Oct-13 CPD-53045 10/16

www.epson.com/documentscanners