



G-Tek® PolyKor®

Seamless Knit PolyKor® Blended Glove with
Foam Nitrile Coated Grip on Palm & Fingers -
Touchscreen

- Seamless construction offers increased comfort and breathability
- PolyKor™ shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Foam Nitrile coatings are breathable and durable, designed with a cell structure that disperse fluids on contact for an improved grip
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- Reinforced thumb crotch for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Knit wrist helps prevent dirt and debris from entering the glove



Technical Data

Color	Gray
Sizes Available	XXS-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	12.60 x 11.02 x 11.81
Case Weight (lbs)	12.13
Country of Origin	Viet Nam
Liner Material	PolyKor
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Foam
Gauge	18
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Touchscreen Compatible, Reinforced Thumb Crotch
Certifications	Silicone Free
Product Circularity	Reusable / Launderable

Performance Data

Cut Level	A2
ANSI Abrasion Level	6
ANSI Puncture Level	3
EN 388	4X42B

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-07

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
16-328/XXS	Gray	XXS	616314880346	10616314880343	20616314880340
16-328/XS	Gray	XS	616314719820	10616314719827	20616314719824
16-328/S	Gray	S	616314719868	10616314719865	20616314719862
16-328/M	Gray	M	616314719905	10616314719902	20616314719909
16-328/L	Gray	L	616314719943	10616314719940	20616314719947
16-328/XL	Gray	XL	616314719981	10616314719988	20616314719985
16-328/XXL	Gray	2XL	616314720024	10616314720021	20616314720028