




EAN:	4013288111661	Size:	140x115x45 mm
Part number:	05104653001	Weight:	279 g
Article number:	849/855/867/18	Country of origin:	CZ
		Customs tariff number:	82079030

- Ideal for mobile repair and assembly work
- Rapidaptor holder for rapid bit change
- 1/4" drive suitable for power screwdrivers
- Rapidaptor universal holder, wood twist drill bits and bits with 1/4" drive
- In practical and robust belt pouch

18-piece wood twist drill bit and bit set. High quality, metal twist drill bits for precise, splinter-free drilling in soft wood, hard wood and laminated panel material. Made out of high speed steel (HSS). A finely-tuned material elasticity provides for great durability. Very good concentricity. The hexagonal shaft ensures very good power transfer. The Rapidaptor universal holder ensures rapid bit change without any extra tools. Drive: 1/4" hexagon, suitable for holders with take-up as per DIN ISO 1173-D 6.3.

Web link
<https://www.wera.de/en/05104653001>

Wera - 849/855/867/18
 05104653001 - 4013288111661

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Twist drill bits for wood applications



Twist drill bits - for wood applications1/4" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173)Hexagon shaft for very high torque transferHSS = high speed steelFinely adjusted material elasticity for long service lifeExcellent concentricityTough-absorbing tempered bits for particularly long service life

Rapidaptor holder



Lightning-fast bit change without any extra tools. One-handed operation. With fast-rotating sleeve for easy wielding of the screwdriver.

Magnetic



Bit holders, magnetic, for easier application of the screw

TH-Bits



TH-Bits are hard bits with a torsion zone. Torsion bits absorb the damaging peak torque loads in the torsion zone. This prevents premature wear and enhances the service life of the bits.

Chuck-all




The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Rapid-in and self-lock




The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Single-hand function



Every function of the Rapidator quick-release chuck, such as inserting or releasing bits, can be carried out with one hand. This is faster, more economical and more ergonomic. There are no unnecessary manoeuvres.

Web link

<https://www.wera.de/en/05104653001>

Wera - 849/855/867/18
05104653001 - 4013288111661

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

889/4/1 K Rapidaptor Universal Bit Holder, 1/4" x 50 mm



05052502001

1x 1/4" x 50 mm



849 HSS Twist Wood Drill Bits, 3 x 70 mm



05104600001

1x 3 x 70 mm

05104601001

1x 4 x 74 mm

05104602001

1x 5 x 85 mm

05104603001

1x 6 x 95 mm

05104604001

1x 8 x 110 mm



855/1 TH bits, PZ 1 x 25 mm



05056910001

2x PZ 1 x 25 mm

05056915001

3x PZ 2 x 25 mm

05056925001

1x PZ 3 x 25 mm



867/1 TORX® bits, TX 10 x 25 mm



05066485001

1x TX 10 x 25 mm

05066486001

1x TX 15 x 25 mm

05066487001

1x TX 20 x 25 mm

05066488001

1x TX 25 x 25 mm

05066490001

1x TX 30 x 25 mm

05066491001

1x TX 40 x 25 mm



Web link

<https://www.wera.de/en/05104653001>

Wera - 849/855/867/18

05104653001 - 4013288111661

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de