HOLEX

LED rechargeable rod light, Length: 220mm

Order data

Order number	081564 220
GTIN	4067263252566
Item class	02A

Description

Version:
Foldable and slim LED cordless work lights with **three lighting options.** Can be used in many applications due to the slim design and two magnets.
· **One spotlight and two main lights.**
· **Front main light dimmable in 2 light levels.**
· **can be folded 180°.**
· **Battery charge is always clearly visible through the LED display.**
Function:
IP20: Protected against penetration by foreign bodies with ∅ < 12 mm, however touching should be avoided, and offers no protection against water.
Supplied with:
Supplied with USB-C charging cable.

Technical description

IP Index of Protection	IP 20
Weight	61 g

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Bulb	LED module
Power supply	Mains operated
Illumination	50 - 100 lm
Illumination time	3 - 6 h
Overall width	30 mm
Type of product	Inspection lamp