HOLEX

Tap wrench, adjustable, Type: 2

Order data

Order number	148410 2
GTIN	4062406208196
Item class	12L

Description

Version:
With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.
For **standard** use: Zinc die-cast body.
Standard: DIN 1814
Capacity ☐: 3 - 9 mm
for hand taps DIN 352: M4 – M12
for hand reamer ∅ DIN 206: 5 - 10 mm
Overall length: 265 mm

Technical description

for hand reamer ∅ DIN 206	5 - 10 mm
Overall length	265 mm
Capacity ☐	3 - 9 mm
for hand taps DIN 352	M4 – M12
Standard	DIN 1814
Type of product	Tap wrench