



Technical Data



Bouton® Optical ECO Series™ Bio-Based Full Frame Safety Glasses with Orange Frame, Gray Lens and Anti-Scratch / FogLess® 3Sixty™ Coating

- FogLess® 3Sixty™ is an enhanced hydrophobic bonded lens coating that repels moisture and prevents fog from gathering
- Modern styling with extended lens coverage and lightweight ergonomic brow guard, to help keep debris out of eyes
- Manufactured from bio-based raw materials, reducing dependency on fossil resources
- Flexible temples provide a comfortable fit on larger head sizes
- Soft rubber nose pads designed for an ergonomic fit and all-day comfort
- Frame construction includes metal screws for durability
- ANSI Z87.1+ rated to protect the industrial athlete
- U6-rated UVA and UVB protection
- 8-base curved lens for a wide field of view
- Lens Coating: Anti-scratch is a hardcoat treatment that toughens the lens surface for a longer product life with fewer scratches.
- ⚠️ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	22.64 x 11.42 x 19.69
Case Weight (lbs)	14.11
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Rimless
Lens Color	Gray
Frame Fit	Universal
Lens Coating	Anti-Scratch, FogLess 3Sixty
Bridge	Molded
Temple	Spatula
Base Curve	8
Construction	Womans Fit
Certifications	TAA Compliant
Product Circularity	Contains Bio-Based Materials Contains Recycled Materials

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-10

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-15-0000	Orange	Clear	Clear	AS	198987006884	10198987006881	20198987006888
250-15-0020	Orange	Clear	Clear	AS/AF	848309084310	10848309084317	20848309084314
250-15-0021	Orange	Tinted	Gray	AS/AF	198987006921	10198987006928	20198987006925
250-15-0029	Orange	Tinted	Amber	AS/AF	198987006648	10198987006645	20198987006642
250-15-0520	Orange	Clear	Clear	AS/FL360	198987006969	10198987006966	20198987006963
250-15-0523	Black	Tinted	Gray	AS/FL360	198987007003	10198987007000	20198987007007
250-15-5000	Black	Clear	Clear	AS	198987007409	10198987007406	20198987007403
250-15-5020	Black	Clear	Clear	AS/AF	198987007560	10198987007567	20198987007564
250-15-5520	Black	Clear	Clear	AS/FL360	198987007607	10198987007604	20198987007601
250-15-5523	Black	Tinted	Gray	AS/FL360	198987007645	10198987007642	20198987007649
250-15-5529	Black	Tinted	Amber	AS/FL360	198987007683	10198987007680	20198987007687
250-151-0020	Black				198987022570	10198987022577	20198987022574

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated