HOLEX

Set of parallels

Order data

Order number	366750
GTIN	4045197293619
Item class	32D

Description

Version:
Ground in pairs, hardness 60 HRC.
Accuracy: height tolerance ± 0.01 mm; width tolerance ± 0.02 mm.
Application:
In high precision work for parallel mounting of components in machine vices or jigs.

Technical description

Height	35 mm
Height	22 mm
Height	45 mm
Height	18 mm
Height	30 mm
Height	50 mm
Height	16 mm
Height	40 mm
Height	26 mm
Height	32 mm
Height	24 mm

Height	14 mm
Height	20 mm
Height	28 mm
Length	150 mm
Width	10 mm
Number of strips	14 pair
Type of product	Pairs of parallels

Accessories

Single pair of parallels for366750 size 150×10 Width 45 mm	366755 45
Single pair of parallels for366750 size 150×10 Width 28 mm	366755 28
Single pair of parallels for366750 size 150×10 Width 35 mm	366755 35
Single pair of parallels for366750 size 150×10 Width 30 mm	366755 30
Single pair of parallels for366750 size 150×10 Width 32 mm	366755 32
Single pair of parallels for366750 size 150×10 Width 14 mm	366755 14
Single pair of parallels for366750 size 150×10 Width 50 mm	366755 50
Single pair of parallels for366750 size 150×10 Width 26 mm	366755 26
Single pair of parallels for366750 size 150×10 Width 20 mm	366755 20
Single pair of parallels for366750 size 150×10 Width 22 mm	366755 22
Single pair of parallels for366750 size 150×10 Width 24 mm	366755 24
Single pair of parallels for366750 size 150×10 Width 40 mm	366755 40
Single pair of parallels for366750 size 150×10 Width 16 mm	366755 16
Single pair of parallels for366750 size 150×10 Width 18 mm	366755 18
Spare wooden case for pairs of parallels Type L1	366754 L1