




EAN:	4013288228321	Size:	165x75x55 mm
Part number:	05075850001	Weight:	370 g
Article number:	7515/7	Country of origin:	CZ
		Customs tariff number:	82041100

- Bicycle tool set
- Torque screwdriver with quick torque adjustment
- Easy and quick torque setting
- Fixed position (Torque Lock) for unlimited tightening and loosening moments
- Secure slip-over torque function for clockwise/anti-clockwise torque-control
- Quick and easy setting of the selectable tightening torques (2.0; 3.0; 4.0; 5.0; 6.0 Nm)
- For bits with 1/4" external hexagon drive, also suitable for socket wrench inserts via adapter - ideal for bike operations
- Take it easy tool finder: colour coding according to profile and size

7-piece tool set. For professional screwdriving/professional fine adjustment AND for torque-controlled screwdriving. Secure slip-over torque mechanism with quick clockwise/counterclockwise setting and five selectable tightening torques (2.0; 3.0; 4.0; 5.0; 6.0 Nm) and one fixed position (Torque Lock) for unlimited loosening and tightening moments. Quick-release holder for high robustness. Ideal for bike operations. Suitable for bits with 1/4" external hexagon drive. 6 tough bits (50 mm length), profile and size of the bits are easily recognized thanks to the Wera Take it easy Tool finder with its colour codes and labels.



Web link
<https://www.wera.de/en/05075850001>

Wera - 7515/7
 05075850001 - 4013288228321

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Five selectable tightening torques



Torque screwdriver with quick torque adjustment




Five selectable tightening torques (2.0; 3.0; 4.0; 5.0; 6.0 Nm) and one fixed position (Torque Lock) for unlimited tightening and loosening moments.

Setting with Speed




Rapid setting of the selectable tightening torques.

Excess-load signal



Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Take it easy tool finder




Take it easy tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.

Storage and transport



Storage and transport in a robust and compact textile roll pouch, so the tool is always close at hand.

Flexible due to hook-and-loop fastener strips



The textile box features a fleece zone at the back. Using the provided self-adhesive hook-and-loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.

Web link

<https://www.wera.de/en/05075850001>

Wera - 7515/7

05075850001 - 4013288228321

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Set contents:

7515 Kraftform Safe-Torque Speed Torque screwdriver, 2-6 Nm, 1/4" x 2.0 Nm x 3.0 Nm x 4.0 Nm x 5.0 Nm x 6.0 Nm x 147.5 mm

05075815001

1x 1/4" x 2.0 Nm x 3.0 Nm x 4.0 Nm x 5.0 Nm x 6.0 Nm x 147.5 mm



867/4 BTZ TORX® bits, TX 10 x 50 mm

1x TX 10 x 50 mm

1x TX 25 x 50 mm



840/4 BTZ bits, 2.5 x 50 mm

1x 2.5 x 50 mm

1x 3 x 50 mm

1x 4 x 50 mm

1x 5 x 50 mm



Web link

<https://www.wera.de/en/05075850001>

Wera - 7515/7

05075850001 - 4013288228321

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de