Giza | 10372WTSBR

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____

PRODUCT DESCRIPTION

A glossy White glass shade, conical in form, is combined with sharp-lined bands of metal finished in your choice of Polished Nickel or Satin Brass to create a pyramid of softly diffused light. Squared off trapezoidal chain loops connect to squared chain links allowing for over ten feet of adjustment. Though modern with its angular form, this pendant applies traditional metalwork details to create a timeless piece perfect for over a kitchen island or bedside.

*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 5" L x 5" W x 8.5" H
MAX OAH	: 46.5" OAH
CANOPY	: 5" W x 0.86" H x 5" L
HANGING WEIGHT	: 3.04 lb

LAMPING

INPUT VOLTAGE	: 120V
BULB	: 1 x 60W Incandescent E26 , 40W Total
BULB INCLUDED	: (Not Included)
DIMMABLE	: Y

FINISHES OPTION

Polished Nickel

Satin Brass

GLASS

White WT

MATERIAL

Steel + Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

MAXIM® LIGHTING

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com