Neoclass | 30054CLBKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____

PRODUCT DESCRIPTION

Two tone frames of Black or White with internal Gold frames provides a neoclassical approach to the squared coach lantern. The sconces jut out from the wall on well-defined trusses that add a contemporary element. Delivering classic design that suits most exteriors, this collection adds interest in the interior contrasting frame of Gold that secures clear glass panes to diffuse the lamp within.

*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 7" W x 18" H x 8.5" Ext
BACK PLATE	: 4.75" W x 8" H x 3" HCO
HANGING WEIGHT	: 3.08 lb

LAMPING

INPUT VOLTAGE	: 120V
BULB	: 2 x 40W Incandescent E12 Candelabra , 120W Total
BULB INCLUDED	: (Not Included)
DIMMABLE	:

FINISHES OPTION

Black / Gold

White/Gold

GLASS

Clear CL

MATERIAL

Aluminum, Glass

RATINGS

Wet Location

ADDITIONAL

INSTALL UP/DOWN: Down
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

MAXIM® LIGHTING

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com