Cabana | 3035CDBK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____

PRODUCT DESCRIPTION

A dual framed structure creates dimension on these outdoor lighting fixtures that is both contemporary and transitional. The constructionÂ consists ofÂ two frames of square tubing and squared components. The inner frame'sÂ Clear Seedy glass reduces glare from the lightÂ and appears dirt-free for longer periods. This is a comprehensive collection to brighten all areas of your outdoorÂ space, available in various sized sconces as well asÂ hanging and post configurations.

*height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 7" W x 18" H x 8" Ext
BACK PLATE	: 4.75" W x 6.25" H x 3" HCO
HANGING WEIGHT	: 5.5 lb

LAMPING

INPUT VOLTAGE	: 120V
BULB	: 1 x 60W Incandescent E26 Medium , 60W Total
BULB INCLUDED	: (Not Included)
DIMMABLE	: Y

FINISHES OPTION

Black

GLASS

Seedy CD

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Down
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

MAXIM® LIGHTING

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com