



jalas® GRAN PREMIO 1558 GP

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S3, P, HRO, CI, HI, FO, SC

Learn more

LOW AND WIDE FOR TOUGH CONDITIONS

Low-cut shoe with extra width. Excellent protection in harsh environments. BOA® Fit System for perfect fit and easy putting on and taking off. Nail protection insert in steel and toe cap in aluminium. PU midsole, rubber outsole and upper material in PU-coated leather.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- Wide fit
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Polstered shaft edge
- Ventilating insole
- BOA® Fit System
- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

BOA DIALED IN. PRECISION FIT. Xrd PROTECTION LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Warm surfaces, Environments with risk for outsole penetration, Oily and greasy environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Wide
COLLECTION Gran Premio
UPPER MATERIAL PU-coated leather, Textile
PRONOSE MATERIAL PU
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyamide
INSOLE JALAS 8103 FX2 Pro-X
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.31 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2022
S3, P, HRO, CI, HI, FO, SC

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Wide fit
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	1558-35	6408487513824
36	3	4	5	1558-36	6408487513848
37	4	5	6	1558-37	6408487513862
38	5	5.5	6.5	1558-38	6408487513886
39	6	6.5	7.5	1558-39	6408487513909
40	6.5	7.5	8.5	1558-40	6408487513923
41	7	8	9	1558-41	6408487513947
42	8	9	10	1558-42	6408487513961
43	9	9.5	11	1558-43	6408487513985
44	10	10.5	11.5	1558-44	6408487514005
45	10.5	11	12.5	1558-45	6408487514029
46	11	12	13	1558-46	6408487514043
47	12	13	14	1558-47	6408487514067
48	13	13.5	14.5	1558-48	6408487514081
49	14	14.5	15.5	1558-49	6408487514104
50	15	15.5	16.5	1558-50	6408487514128

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.