PRODUCT DESCRIPTION

Wafer was designed for the discriminate consumer who wants the low profile look of recessed without the high cost. Manufactured of die cast aluminum, Wafer brings ultimate heat dissipation to its edge lit technology. Edge lighting gives very even light distribution while dispersing heat over a larger area. The result of this is longer LED life and better light diffusion.

MEASUREMENTS

DIMENSION	: 22" L x 22" W x 0.5" H
HANGING WEIGHT	: 8.95 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,375 Rated (2,700 Del.)
BULB	: 1 x 32W LED PCB Integrated , 32W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Only at 120V
CRI	: 90 CRI
COLOR_TEMP	: 4000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

White

GLASS

White WT

RATINGS

cETLus
Wet Location
Energy Star
CA Title 24
ADA

ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

MAXIM® LIGHTING

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com