



TEGERA® 432

Learn more

WHITE COLOR FOR EASIER DIRT DETECTION

Cut resistant glove (level B) in white color for easier dirt detection, suitable for versatile applications. A combination of high comfort, flexibility, and medium cut protection thanks to the design and CRF® Technology. Has a breathable back and PU coating on palm with smooth finish which provides a good grip on dry to slight moist surfaces.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Comfortable

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Clean environments, Moist environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Inspection work, Machine operating, Installation work, Warehouse work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Pulp and paper, Rubber and plastics manufacturing, Transport equipment manufacturing, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Cut resistant gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL CRF® Technology, HPPE, Nylon, Spandex
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR White
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 6.5 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Elastane, Nylon
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II

EAC

EN ISO 21420:2020

EN 388:2016+A1:2018 4X42B

ANSI A2 CUT

ANSI 6 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
5	XXS	432-5	7340118329857
6	XS	432-6	7340118320403
7	S	432-7	7340118320410
8	M	432-8	7340118320427
9	L	432-9	7340118320434
10	XL	432-10	7340118320380
11	XXL	432-11	7340118320397

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.