



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288120892 | <b>Size:</b>                  | 105x44x28 mm |
| <b>Part number:</b>    | 05003627001   | <b>Weight:</b>                | 93 g         |
| <b>Article number:</b> | 8790 HMC      | <b>Country of origin:</b>     | TW           |
|                        |               | <b>Customs tariff number:</b> | 82042000     |

- 1/2" Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- With Take it easy tool finder: colour coding by size

The Wera manual and machine socket (ISO 2725 part 3) can be used in manual and machine operations. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. Slip-proof for easy grip even with oily hands. With ball stop groove. For external hexagon screws and bolts. Made of matte chrome-plated chrome-vanadium.

**Web link**  
<https://www.wera.de/en/05003627001>

Wera - 8790 HMC  
05003627001 - 4013288120892

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Take it easy tool finder system

## Manual and machine sockets



Incredibly fast Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions









Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

## Further versions in this product family:

|             |                        |  |  |  |  |  |  |
|-------------|------------------------|---|---|---|---|---|---|
|             |                        | mm  | inch  | mm  | mm  | mm  | mm  |
| 05003601001 | leuchtgelb_yello<br>wC | 10.0  | -   | 37.0  | 15.5  | 24.0  | 17.0  |
| 05003602001 | cyan_2985C             | 11.0  | -   | 37.0  | 16.5  | 24.0  | 17.0  |
| 05003603001 | schwarz_blackC         | 12.0  | -   | 37.0  | 17.5  | 24.0  | 17.0  |
| 05003604001 | tuerkis_339C           | 13.0  | -   | 37.0  | 19.0  | 24.0  | 17.0  |
| 05003605001 | pink_241C              | 14.0  | -   | 37.0  | 20.0  | 24.0  | 17.0  |
| 05003606001 | weiss                  | 15.0  | -   | 37.0  | 21.0  | 24.0  | 17.0  |
| 05003607001 | violett_2735C          | 16.0  | -   | 37.0  | 22.5  | 24.0  | 17.0  |
| 05003608001 | rot_200C               | 17.0  | -   | 37.0  | 24.0  | 26.0  | 17.0  |
| 05003609001 | leuchtgruen_37<br>5C   | 18.0  | -   | 37.0  | 25.0  | 26.0  | 17.0  |
| 05003610001 | blau_307C              | 19.0  | -   | 37.0  | 26.5  | 26.0  | 20.0  |
| 05003611001 | leuchtpink_232<br>C    | 20.0  | -   | 37.0  | 28.0  | 26.0  | 20.0  |
| 05003612001 | gruen_363C             | 21.0  | -   | 37.0  | 29.0  | 26.0  | 20.0  |
| 05003613001 | leuchtgelb_yello<br>wC | 22.0  | -   | 37.0  | 30.5  | 26.0  | 20.0  |
| 05003614001 | cyan_2985C             | 24.0  | -   | 37.0  | 33.0  | 28.0  | 20.0  |
| 05003615001 | schwarz_blackC         | 27.0  | -   | 40.0  | 36.5  | 32.0  | 23.0  |

## Web link

<https://www.wera.de/en/05003627001>

Wera - 8790 HMC

05003627001 - 4013288120892

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

|                    |                      |          |               |             |             |             |             |
|--------------------|----------------------|----------|---------------|-------------|-------------|-------------|-------------|
| 05003616001        | tuerkis_339C         | 30.0     | -             | 42.0        | 40.0        | 34.0        | 25.0        |
| 05003617001        | pink_241C            | 32.0     | -             | 42.0        | 42.0        | 36.0        | 25.0        |
| 05003618001        | rot_200C             | -        | 3/8"          | 37.0        | 15.5        | 24.0        | 17.0        |
| 05003619001        | violett_2735C        | -        | 7/16"         | 37.0        | 16.5        | 24.0        | 17.0        |
| 05003620001        | tuerkis_339C         | -        | 1/2"          | 37.0        | 19.0        | 24.0        | 17.0        |
| 05003621001        | pink_241C            | -        | 9/16"         | 37.0        | 20.0        | 24.0        | 17.0        |
| 05003622001        | weiss                | -        | 19/32"        | 37.0        | 21.0        | 24.0        | 17.0        |
| 05003623001        | schwarz_blackC       | -        | 5/8"          | 37.0        | 22.5        | 24.0        | 17.0        |
| 05003624001        | cyan_2985C           | -        | 11/16"        | 37.0        | 25.5        | 26.0        | 17.0        |
| 05003625001        | gelb_123C            | -        | 3/4"          | 37.0        | 26.5        | 26.0        | 20.0        |
| 05003626001        | leuchtpink_232<br>C  | -        | 25/32"        | 37.0        | 28.0        | 26.0        | 20.0        |
| <b>05003627001</b> | <b>blau_307C</b>     | <b>-</b> | <b>13/16"</b> | <b>37.0</b> | <b>29.0</b> | <b>26.0</b> | <b>20.0</b> |
| 05003628001        | leuchtgruen_37<br>5C | -        | 7/8"          | 37.0        | 30.5        | 26.0        | 20.0        |
| 05003629001        | rot_200C             | -        | 15/16"        | 37.0        | 33.0        | 28.0        | 20.0        |
| 05003630001        | violett_2735C        | -        | 31/32"        | 37.0        | 33.0        | 28.0        | 20.0        |
| 05003631001        | tuerkis_339C         | -        | 1"            | 40.0        | 36.5        | 32.0        | 23.0        |
| 05003632001        | pink_241C            | -        | 1 1/16"       | 40.0        | 36.5        | 32.0        | 23.0        |
| 05003633001        | weiss                | -        | 1 1/8"        | 40.0        | 40.0        | 34.0        | 23.0        |
| 05003634001        | schwarz_blackC       | -        | 1 3/16"       | 42.0        | 40.0        | 34.0        | 25.0        |
| 05003635001        | cyan_2985C           | -        | 1 1/4"        | 42.0        | 42.0        | 36.0        | 25.0        |

**Web link**
<https://www.wera.de/en/05003627001>

Wera - 8790 HMC

05003627001 - 4013288120892

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de