USSK28-20MM-1/2"-F

Ruland USSK28-20MM-1/2"-F, 20mm x 1/2" Single Universal Joint, Friction Bearing, Steel, Set Screw With Keyway, 1.745" (44.3mm) OD, 5.000" (127.0mm) Length



Description

Ruland USSK28-20MM-1/2"-F is a single cardan friction bearing universal joint with 20mm x 0.5000" bores, 6mm x 1/8" keyways, 1.745" (44.3mm) OD, 5.000" (127.0mm) length, and 5/16-18 set screws. It is ideal for applications with space constraints and has higher torque capacity than equivalently sized double universal joints. This plain bearing universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 45° when compared to commodity style single universal joints. USSK28-20MM-1/2"-F is made from high grade alloy steel for durability and high strength. It can be combined with boot UBOOT28/44-NI-KIT to protect the joint from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This single cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	20 mm	**Small Bore (B2)**	0.5000 in
Keyway (K1)	6 mm	**Keyway (K2)**	1/8 in
B1 Max Shaft Penetration	1.610 in (40.9 mm)	**B2 Max Shaft Penetration**	1.610 in (40.9 mm)
Joint Outer Diameter (OD)	1.745 in (44.3 mm)	**Bore Tolerance**	+0.0010 in / -0.0000 in (+0.025 mm / -0.000 mm)
Length (L)	5.000 in (127.0 mm)	**Yoke Length (LY)**	2.500 in (63.5 mm)
Hub Depth (LH)	1.610 in (40.9 mm)	**Broached Set Screw**	5/16-18
Screw Finish	Black Oxide	**Peak Torque**	14,500 in-lb (1,638.3 Nm)
Rated Torque	2,900 in-lb (327.7 Nm)	**Max Operating Angle**	45°
Material Specification	Alloy Steel	**Manufacturer**	Belden Universal
Country of Origin	USA	**Recommended Lubricant**	LUBRIPLATE No. 1200-2
Matching Boot Cover	UBOOT28/44-NI-KIT	**UPC**	63452934165
Tariff Code	8483.60.4000	**UNSPC**	25173810
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.		