



EAN: 4013288182159

Part number: 05004090001

Article number: 8006 SC 1

Size: 325x150x75 mm

Weight: 2624 g

Country of origin: CZ

Customs tariff number: 82041100

- Switchover lever for convenient direction change
- Fine-pitched with 72 teeth for a return angle of only 5°
- Compact textile box with high robustness, low weight and volume
- Colour coding of the sockets according to size
- Smooth rotary mechanism for a secure hold and easy access of the tools

Zyklop Hybrid ratchet set, 1/2" drive, metric. Including Zyklop Hybrid ratchet and Hybrid handle extension.




Web link
<https://www.wera.de/en/05004090001>

Wera - 8006 SC 1
05004090001 - 4013288182159

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Ball lock



The ball lock ensures sockets and accessories fit securely, providing increased safety during operation. A short press on the release button allows the tool to be changed quickly.

Kraftform




Multi-component Kraftform handle for optimum pressure and tensile loads.

Higher torque transfer



Larger overall length for higher torque transfer.

Hybrid extension




Even more torque can be applied by using the extension.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Secure hold and easy removal



The all new smooth turning mechanism guarantees both secure and rattle-free storage, yet allows easy removal of the tool.

Set contents:

8006 C Zyklop Hybrid Ratchet with switch lever and 1/2" drive, 1/2" x 281 mm



05003780001

1x 1/2" x 281 mm



8797 C Zyklop Hybrid extension, 271 mm

05003781001

1x 271 mm



8794 LC Zyklop extension with free-turning sleeve, long, 1/2", 1/2" x 250 mm



05003638001

1x 1/2" x 250 mm



8790 HMC HF Zyklop socket with 1/2" drive with holding function, 10 x 37 mm



05003730001

1x 10 x 37 mm

05003731001

1x 11 x 37 mm

05003732001

1x 12 x 37 mm

05003733001

1x 13 x 37 mm

05003734001

1x 14 x 37 mm

05003735001

1x 15 x 37 mm

05003736001

1x 16 x 37 mm

05003737001

1x 17 x 37 mm

05003738001

1x 18 x 37 mm

05003739001

1x 19 x 37 mm



Hook and Loop Fastener Strip 240, 50 x 240 mm

1x 50 x 240 mm



Web link

<https://www.wera.de/en/05004090001>

Wera - 8006 SC 1

05004090001 - 4013288182159

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de