

Self-Igniting Swirl Combustion Torch Tips



Twister[®] 2 Kits


FOR U.S. JOBS
UNIWELD EMPLOYS OVER 300 WORKERS

Twister[®] 2 self-igniting Torch Kits feature swirl combustion technology that produces a high energy efficient flame. The flame remains stable, even in windy conditions. The self-igniting tip "quick connects" to the ergonomically designed handle.



KT2A5MCT

512 Carrying Stand
U.S. Patent No. 4,294,448



KT2A5

GAUGES WITH PROTECTIVE RUBBER BOOTS



KT2A5T

2 Air/Acetylene

	Part#	UPC#	Regulator	Handle	Tips	Carrying Stands	Tanks*
Quick Connect	KT2A5	89650	RB Acetylene Regulator	TH6	T2A-5 Twister [®] Tip	w/o	w/o
	KT2A5T	89651	RB Acetylene Regulator	Quick Connect Handle with Rear Control Valve	T2A-5 Twister [®] Tip	502	"B" Acetylene Tank
	KT2A5MC	89652	RMC Acetylene Regulator		T2A-5 Twister [®] Tip	w/o	w/o
	KT2A5MCT	89653	RMC Acetylene Regulator		T2A-5 Twister [®] Tip	512	"MC" Acetylene Tank

Regulators fitted with protective rubber gauge boots. Kits include H12 [12.5 ft.] Acetylene Hose, W05 Tank Key w/chain.* Tanks shipped empty.



Uniweld Products, Inc. Fort Lauderdale, FL 33312 U.S.A. Customer Service: 800.323.2111
info@uniweld.com • www.uniweld.com

21

Quick Connect and Screw Connect



Twister® Kits

FOR U.S. JOBS
UNIWELD EMPLOYS OVER 300 WORKERS




89602



89605

GAUGES WITH PROTECTIVE RUBBER BOOTS



89600

2 Air/Acetylene

	Part#	Regulator	Handle	Tips	Carrying Stands	Tanks*
Quick Connect	89600	RB Acetylene Regulator	TH6 Quick Connect Handle Rear Control Valve	A-3, A-11 Twister® Tips	w/o	w/o
	89602	RB Acetylene Regulator		A-3, A-11 Twister® Tips	502	"B" Acetylene Tank
	89603	RMC Acetylene Regulator		A-3, A-11 Twister® Tips	w/o	w/o
	89605	RMC Acetylene Regulator		A-3, A-11 Twister® Tips	512	"MC" Acetylene Tank
	89620	RB Acetylene Regulator		A-5 Twister® Tip	w/o	w/o
	89621	RB Acetylene Regulator		A-5 Twister® Tip	502	"B" Acetylene Tank
	89622	RMC Acetylene Regulator		A-5 Twister® Tip	w/o	w/o
	89623	RMC Acetylene Regulator		A-5 Twister® Tip	512	"MC" Acetylene Tank
	89628	RB Acetylene Regulator		A-5, A-14 Twister® Tips	w/o	w/o
	89629	RB Acetylene Regulator		A-8 Twister® Tip	w/o	w/o
Screw Connect	89608	RB Acetylene Regulator	TH3 Screw Connect Handle Rear Control Valve	AS-3, AS-11 Twister® Tips	w/o	w/o
	89609	RB Acetylene Regulator		AS-3, AS-11 Twister® Tips	502	"B" Acetylene Tank
	89610	RMC Acetylene Regulator		AS-3, AS-11 Twister® Tips	w/o	w/o
	89611	RMC Acetylene Regulator		AS-3, AS-11 Twister® Tips	512	"MC" Acetylene Tank
	89624	RB Acetylene Regulator		AS-5 Twister® Tip	w/o	w/o
	89625	RB Acetylene Regulator		AS-5 Twister® Tip	502	"B" Acetylene Tank
	89626	RMC Acetylene Regulator		AS-5 Twister® Tip	w/o	w/o
	89627	RMC Acetylene Regulator		AS-5 Twister® Tip	512	"MC" Acetylene Tank

Regulators fitted with protective rubber gauge boots. Kits include H12 [12.5 ft.] Acetylene Hose, W05 Tank Key w/chain. *Tanks shipped Empty.



Uniweld Products, Inc. Fort Lauderdale, FL 33312 U.S.A. Customer Service: 800.323.2111
info@uniweld.com • www.uniweld.com

23



Portable Kit with Swivl-it Fitting

LP Thruster® Kits

Lightweight, portable kits featuring "Swivl-it" fittings that eliminate hose kinking and wrist fatigue. Solder up to 1.5" and braze up to 1" copper tubing. Metal carrying stand holds two disposable cylinders.

FOR U.S. JOBS
UNIWELD EMPLOYS OVER 300 WORKERS

TARGET HEAT



TARGET HEAT AREA
THE MOST EFFICIENT AREA
FOR HEAT TRANSFER.



KTSQ2

**Swivl-it
Kits**

Part#	UPC#	Regulator	Tips	Handle	Hose	Swivl-it™	Carrying Stand
KTS2	89208	RP3B	LPT4	TH5B	HLP14B	HCC39	512
KTSQ2	89205	RP3B	LPTQ4	TH7B	HLP14B	HCC39	512

Disposable cylinders not included in kits and are sold separately.

500,000 BTU Weed Burner

Scorcher®

A Propane Gas Torch Kit with hundreds of uses, including weed burning, asphalt repair, ice melting, debris burning, fire ant mounds and roofing repairs. Hooks up to a standard 20 lb. Propane (barbeque) tank.

All Steel Handle

10' U.L. Listed Propane Hose with P.O.L. Safety Valve

Scorcher®

Part#	UPC#	Description	Hose	Accessories
WB500	00700	Weed Burner 10' w/P.O.L. Safety Valve	Flint Lighter Included	

Sold in units of 6 only.



Flint Lighter included



All Steel Torch Head



WB500

3 Air/LP



Uniweild Products, Inc. Fort Lauderdale, FL 33312 U.S.A. Customer Service: 800.323.2111
info@uniweild.com • www.uniweild.com




Plastic and Metal

Carrying Stands


FOR U.S. JOBS
UNIWELD EMPLOYS OVER 300 WORKERS

The rugged Uniweld line of Carrying Stands and Cylinder Trucks provides convenience, portability and organization. All blue enameled steel models feature fitted hand grips and hose holders. The center-balanced blue plastic tote has storage space for cylinders, hoses and accessories.



4 Parts & Accessories

Part#	UPC#	Description
500S	30001	Carrying stand for [1] "MC" tank & [1] "R-Oxy" tank w/utility tray & brazing rod holder
502	30003	Carrying stand for [1] "B" tank w/utility tray & Air/Fuel handle holder
503	30004	Carrying stand with wheels for [1] "B" tank & [1] "R-Oxy" tank
504	30005	Carrying stand with wheels for [1] "MC" or "B" tank & [1] "R-Oxy" or "R40" tank
510	30007	Carrying stand with utility tray for [1] "MC" tank or [2] disposable fuel cylinders and [1] "R-Oxy" tank
511	30008	Molded blue plastic carrying stand for [1] "MC" tank or [1] disposable fuel cylinder and [1] "R-Oxy" tank
512	30009	Carrying stand for [2] disposable fuel cylinders or [1] "MC" tank w/utility tray and Air/Fuel handle holder
515	30012	Nitrogen carrying stand for [1] 20 cu. ft. Nitrogen tank
516	30013	Nitrogen carrying stand for [1] 40 cu. ft. Nitrogen tank
517	30014	Nitrogen carrying stand with wheels for [1] 60 cu. ft. tank



503
Holds
[1] "B" tank
and
[1] "R-Oxy" tank

Carrying Stands	Metal
	Plastic
	Metal



Uniweld Products, Inc. Fort Lauderdale, FL 33312 U.S.A. Customer Service: 800.323.2111
info@uniweld.com • www.uniweld.com