

7 pc. 1/4 in. Drive Deep External Star Socket Set

- For servicing inverted E-series fasteners
- Applications include: electrical switches on GM, domestic vehicle air bags, V6 and V8 engine camshaft adjustment solenoids, specially engine and exhaust pipe flange studs, many European vehicles
- Chrome vanadium steel construction for strength and durability
- Polished chrome plated finish
- Includes socket storage rail



Part #	Size/Contents/Specs	UPC Code	Master Pack	Inner Pack
66320	E4, E5, E6, E7, E8, E10, E11	802090663208	36	6

8 pc. 3/8 & 1/2 in. Drive External Star Deep Socket Set

- For servicing inverted E-series fasteners
- Suitable for many applications on both foreign and domestic vehicles, including electrical switches on GM, domestic vehicle air bags, V6, and V8 engine camshaft adjustment solenoids, engine and exhaust pipe flange studs
- Chrome vanadium steel construction for strength and durability
- Polished and chrome-plated finish
- Includes socket storage rail



Part #	Size/Contents/Specs	UPC Code	Master Pack	Inner Pack
68302	3/8 in. Dr.: E11,E12,E14,E16 1/2 in. Dr.: E18,E20,E22,E24	802090683022	24	6

33 pc. Multi-Bit Precision Screwdriver Set

- Soft comfort grip handle extends from 4-13/16 in. to 7-1/4 in. (122 mm to 184 mm)
- 7.9 in. (200 mm) Flexible extension
- Mini magnifier
- Storage case included
- Chrome molybdenum steel bits



Part #	Size/Contents/Specs	UPC Code	Master Pack	Inner Pack
16093	30 Pieces Precision 4 mm hex bits: (7) Slotted: 1, 1.5, 2, 2.5, 3, 3.5, & 4 mm (4) Phillips: PH000, PH00, PH0, & PH1 (2) Pozi: PZ0 & PZ1 (9) Star: T4, T5, T6, T7, T8, T9, T10, T15, & T20 (8) Hex: 0.7, 0.9, 1.3, 1.5, 2.0, 2.5, 3.0, & 4.0 mm	802090160936	72	12

11 pc. Offset Bit Driver

- L-shape driver handle provides straight and 90 degree driving
- 90° low profile driver end is perfect for hard-to-reach spaces
- Powerful magnetic bit retention reduces wobble and minimizes drops
- Durable chrome vanadium steel construction provides more torque for stubborn fasteners
- Overall Length: 4.75 in.
- Includes handy bit and driver handle holder



Part #	Size/Contents/Specs	UPC Code	Master Pack	Inner Pack
16091	Offset bit driver; (3) Phillips: PH1, PH2, and PH3; (3) Slotted: 1/8, 5/32, and 3/16 inch; (2) Hex: 3 & 4 mm; (2) Star: T15 & T20	802090160912	144	18