

S23146

18W/LED/CCT/100-277V/E26

GENERAL SPECIFICATIONS

Wattage:	18W/16W/12W
Lumen Output:	2520L/2240L/1680LL
Color Temperature:	3000K/4000K/5000K
Base:	Medium

50,000 HOURS · ENCLOSED FIXTURE · BALLAST BYPASS · 4KV SURGE PROTECTION · FC · RoHS COMPLIANT

TECHNICAL SPECIFICATIONS

Wattage:	18W/16W/12W
Volts:	100V-277V
HID Equivalent:	75W/50W/40
Filament:	LED
Base:	Medium
ANSI Base:	E26
Finish:	White
Housing Color:	Dark Gray
Hours Rated:	50000H
Color Temperature:	3000K/4000K/5000K

CRI:	80CRI
Lumen Output:	2520L/2240L/1680L
Dimmable:	Yes-Dimmable
Dimming Function:	Dimmable only via the wattage/lumen selectable dial included on lamp
Burning Position:	Base Up, Base Down, or Horizontal
Beam Spread:	300D
Power Factor:	>0.9
Operating Temp:	-40C (-40F) to a maximum of +60C (+140F)
Safety Listing:	cULus - Classified; cULus - Certified; cULus - Listed
Technology:	LED

DIMENSIONS

MOL:	6.29"
MOD:	2.32"
Weight:	0.55

LISTINGS

Safety Listing:	cULus - Classified; cULus - Certified; cULus - Listed
Location Rating:	Damp
Energy Star:	No
UL File Listing:	US/CN - E356817; US/CN - E335148
RoHS Compliant:	Yes
FCC Compliant:	Yes
SDS Class:	LED_Lamp

PACKAGING

Each UPC:	045923231469	Inner UPC:	20045923231463	Case UPC:	10045923231466
Each Quantity:	1	Inner Quantity:	12	Case Quantity:	24
Each Dimensions:	8.27 x 2.83 x 2.83"	Inner Dimensions:	12.20 x 9.25 x 8.86"	Case Dimensions:	19.37 x 12.99 x 10.00"

110 Heartland Blvd.
Brentwood, NY 11717
PH 631-243-2022
FX 631-243-2027

Distribution Centers
New York, Florida,
Texas, Washington,
California, Puerto Rico

National Toll-Free
800-43-SATCO
(800-437-2826)
www.satco.com

Copyright 2022
Satco Products, Inc.
All Rights Reserved
April 18, 2022