1-1337435-0 Product Details

Live Product Chat

1-1337435-0

TE Part Number: 1-1337435-0
Active
Add to Part List

BNC RF Connectors

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Connector Type = BNC
- Jack
- Terminate To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

View all Features | Find Similar Products

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples NEW!

Documentation & Additional Information

Product Drawings:

- BNC BULKHEAD JACK REAR MOUNT CRIMP 75 OHM RG59B/U, 6... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = BNC
- Gender = Jack
- Crimp Type = Hex
- Body Style = Bulkhead
- Grade = Professional
- Body Material = Brass
- Sealed = No
- Isolated = No
- Dielectric Material = PTFE
- Number of Ports = 1
- Panel Thickness (mm [in]) = 2.00 – 5.00 [0.078 – 0.197]
- Flats Dimension = 16.0 A/F
- Gasket Material = White Silicone Rubber

Mechanical Attachment:

- Surface Mountable = No
- Panel Attachment = With
- Panel Attachment Method = Hex Nut
- Panel Attachment Style = Rear Mount
- Panel Cutout = 12.0mm x 12.9mm D-Shape
- Flange Dimension [A/F] (mm [in]) = 17.5 [0.689]
- Flange and Thread Material = Brass
- Lockwasher Material = Mild Steel
- Lockwasher Plating = Nickel

Electrical Characteristics:

- Connector Impedance (Ω) = 75
- Frequency = DC - 2 GHz

Termination Related Features:

- Coaxial Cable Termination Type = Crimp

Body Related Features:

- Hardware Included = No
- Body Plating = Nickel
- Polarized = No
- Ferrule Type = Hex
- Hand Tool No. = 9-1478240-0
- Interchangeable Die Set Number = 9-1478242-0
- Crimp Dimensions = 1.75 + 2.6 + 5.6 + 6.5

Contact Related Features:

- Center Contact Material = Brass
- Center Contact Plating = Gold

Configuration Related Features:

- Coaxial Cable Type (RG/U or Mfg.) = 140, 210, 59B, 62A, Raychem 9524A1311, Raychem 9524A1811, URM 90

Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- Terminate To = Coaxial Cable
- Military Style Number = UG-1808/U
- Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- Packaging Method = Individual
- Packaging Quantity = 50

Other:

- Brand = Greenpar

© 2008 Tyco Electronics Corporation All Rights Reserved