Part Number: 1201150050

Status: Active

Overview: Brad Micro-Change (M12) Connectors

Description: Micro-Change Molded Junction Box, Side Mount, Single Keyway with Mini-Change B-Size Molded Home Run Connector, 6 Ports, PNP, 0.30m Cable Length



Series image - Reference only

Documents:
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Passive Distribution Boxes
Series	120115
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Taxonomy	Passive Distribution Boxes
UPC	78678824064

Physical

Bus I/O	Micro-Change (M12)
Cable Connector Orientation	Straight
Cable Length	N/A
Home Run Cable Length	0.305m
Home Run Connector	Micro-Change (M12) - 8 pole
Home Run Interface	Integrated Connector
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Orientation	Side Mount
Poles	5
Poles (wired)	4
Ports	6
Temperature Range - Operating	-20°C to +90°C
Wiring Configuration	Single I/O per Port

Electrical

Current - Maximum per Contact	4.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC

Material Info

Engineering Number	803P602

Reference - Drawing Numbers

Sales Drawing	SD-120115-008-001

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
120115 Series