Part Number: 1300940238

Status: Active

Overview: Support Grips

Description: Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 31.75-37.85mm (1.250-1.490"), Approximate Break Strength 762.04kg (1680 lbs)

Series image - Reference only

Documents:
Packaging Specification PK-130227-004-001 (PDF)
RoHS Certificate of Compliance (PDF)
Brochure (PDF)

Agency Certification

CSA	LR32159

General

Product Family	Cable Grips
Series	130094
Eye Type	Single
O-Ring	N/A
Overview	Support Grips
Product Name	Standard Duty
Taxonomy	Cable Grips
Type	Support Grip
UPC	78678835034

Physical

Approximate Break Strength	762.04kg (1680 lbs)
Bale Length	0.254m (10.00")
Body Style	Straight
Cable Diameter	31.75-37.85mm (1.250-1.490")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.406m (16.00")
Net Weight	425.110/g
Number of Holes	N/A
Thread Size	N/A

Material Info

Engineering Number	35034

Reference - Drawing Numbers

Packaging Specification	PK-130227-004-001

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
130094 Series