molex
one company › a world of innovation

This document was generated on 09/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1301020140

Status: Active

Overview: Hand Lamps

Description: Super-Safeway Rubber Hand Lamp with 100W Open End Guard, with Receptacle

Series image - Reference only

Documents:

Brochure (PDF) | RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR85374
UL	E59251

General

Product Family	Portable Lighting
Series	130102
NEMA Configuration	N/A
Outlet	Side
Overview	Hand Lamps
Product Name	Super-Safeway
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678860440

Physical

Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	153.92mm (6.060")
Duty	Industrial
Guard Included	Yes
Guard Type	Open End
Height	311.66mm (12.270")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Material Info

Engineering Number	110U

EU ELV
Not Relevant

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130102 Series

This document was generated on 09/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION