Part Number: 1301460110

Status: Active

Overview: Watertite Extreme Wet-Location Wiring Solutions

Description: Watertite Extreme Receptacle Connector, 2 Pole/2 Wire, NEMA L2-20, 250V, Cord Grip Body Size F2, Silicone Husk

Series image - Reference only

Documents:
Drawing (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Wiring Devices
Series	130146
IP Rating	IP69K
NEMA Configuration	NEMA L2-20
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Connector
UPC	78678871360
Physical	
Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	Yes
Poles	2-pole/2-wire
Electrical	
Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V
Material Info	
Engineering Number	27W07
Reference - Drawing Numbers	
Sales Drawing	1301460110-000

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130146 Series