D-181 -3222 -90/9 Product Details



D-181 -3222 -90/9

TE Part Number: 024278 -000

Active

Add to Part List

Shield Terminators

Always ELV Compliant (Statement of Compliance)

Product Highlights:

- Sealing = Splash Resistant
- Cable Temperature Rating = 125 °C
- Jacket Outer Diameter = 2.54 - 5.20 mm
- Shield O.D. (Min.) = 2.15 - 4.60 mm
- With Preinstalled Lead

View all Features | Find Similar Products

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- Coaxial SolderSleeve Device with Pre-installed Lead (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Mechanical Attachment:

- Inside Diameter (mm [in]) = 5.20 [0.205]

Body Related Features:

- Jacket Outer Diameter (mm [in]) = 2.54 – 5.20 [0.100 – 0.205]

Housing Related Features:

- Sealing = Splash Resistant
- Shield O.D. (Min.) (mm [in]) = 2.15 – 4.60 [0.085 – 0.180]
- Preinstalled Lead = With
- Preinstalled Lead Wire Size (mm ^{2} [AWG]) = 0.38 [22]
- MIL or NAS Specification (MIL-S-83519) (NAS 1747) = No
- Length (Max.) (mm [in]) = 21.50 [0.850]

Configuration Related Features:

- Temperature Indication System = Without

Industry Standards:

- RoHS/ELV Compliance = ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was ELV compliant

Conditions for Usage:

- Cable Temperature Rating (°C) = 125
- Operating Temperature (Max.) (°C) = 150

Other:

- Brand = Raychem

© 2008 Tyco Electronics Corporation All Rights Reserved