B07B311BC3 Product Details



Active

View 3D PDF

Military/Aerospace High Performance Relays

B07B311BC3 = 07 10AMP RELAY

B07B311BC3 (1617003-2)

TE Internal Number: 1617003-2

Product Highlights View All

- 07 Full Size Relay Series
- Input Voltage = 26.5 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 10 A
- Non Polarized, Monostable Coil - Magnetic System

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

[+] Feedback

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
MOSFET Driver	Without

Mechanical Attachment	
Mounting Options	Socket

Electrical Characteristics	
Input Voltage (VDC)	26.5
Contact - Rated Current (A)	10
Coil Suppression Diode	Without
Coil Polarity Protection Diode	Without
Coil - Resistance (Ω)	300
Coil Power Measurement	Milliwatts
Coil - Rated Power, DC (mW)	2341
Actuating System	DC
Shock	50G's, 11ms
Vibration	20G's, 10 to 2000Hz

Termination Features	
Termination Type	PC Pins

Body Features	
Enclosure Type	Hermetically Sealed

Configuration Features	
Contact - Arrangement [?]	2 Form C, DPDT, 2 C/O
Coil - Magnetic System	Non Polarized, Monostable
Transistor Driver	Without

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance [?]	Not ELV/RoHS compliant
Lead Free Solder Processes [?]	Not relevant for lead free process

Conditions for Usage	
Temperature Range (°C)	-65 – +125

Other	
Series [?]	07 Full Size Relay
Brand	CII

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved