1969443-2 ✔ ACTIVE

Economy Power 2.5

TE Internal #: 1969443-2

PCB Latches, Locks & Retainers, TPA (Terminal Position Assurance), Wire-to-Board, 2 Position, .098 in [2.5 mm] Centerline, Economy Power 2.5

View on TE.com >

Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Latches, Locks & Retainers

Connector & Contact Retention Accessory Type: **TPA (Terminal Position Assurance)**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **2.5 mm [.098 in]**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Connector & Contact Retention Accessory Type	TPA (Terminal Position Assurance)
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Primary Product Material	Nylon GF
Primary Product Color	Black

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Product Height	2.51 mm[.099 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # 1744423-1
EP 2.5 RCPT CONTACT, 24-20 AWG

TE Part # 2110989-1
EP 2.5 RCPT CONTACT, 26-22 AWG

TE Part # 1744417-2
2 POS EP 2.5 HSG, GLOW WIRE

TE Part # 1969442-2
EP 2.5 TPA Housing, 2 Pos

TE Part # 2299683-2
EP2.5 HDR ASSY 2P VERT W/O BOSS, TAPING

TE Part # 1-1744525-7
3.96 EP HDR ASSY 7P R/A, GW,omit 2&6

TE Part # 1-2299683-1
EP2.5 HDR 2P VERT W/O BOSS, TAPING,RED

TE Part # 1-2299683-2
EP2.5 HDR 2P VERT W/O BOSS, TAPING,RED

TE Part # 1969825-2
EP 2.5 TPA Retainer, 2 Pos

TE Part # 1969825-3
EP 2.5 TPA RETAINER, 3 POS

TE Part # 1969825-4
EP 2.5 TPA RETAINER, 4 POS

TE Part # 1969825-5
EP 2.5 TPA RETAINER, 5 POS

TE Part # 2-2299683-1
EP2.5 HDR 2P VERT W/O BOSS, TAPING,BLUE

TE Part # 2-2299683-2
EP2.5 HDR 2P VERT W/O BOSS, TAPING,BLUE

TE Part # 2299683-1
EP2.5 HDR 2P VERT W/O BOSS, TAPING

TE Part # 3-2299683-1
EP2.5 HDR 2P VERT W/O BOSS, TAPING,BLACK

TE Part # 3-2299683-2
EP2.5 HDR 2P VERT W/O BOSS, TAPING,BLACK

TE Part # 4-2299683-1
EP2.5 HDR 2P VERT W/O BOSS, TAPING,YELLOW

TE Part # 4-2299683-2
EP2.5 HDR 2P VERT W/O BOSS, TAPING,YELLOW

TE Part # 5-2299683-1
EP2.5 HDR 2P VERT W/O BOSS, TAPING,GREEN

Also in the Series | Economy Power 2.5

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(408)

PCB Latches, Locks & Retainers(49)

Rectangular Power Connectors(43)

Wire-to-Board Connector Assemblies & Housings(311)

Wire-to-Board Connector Contacts(6)

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969443-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969443-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1969443-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

7-1773461-6_EP2.5_Connector_Series

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1969443-2_09062018852_dmtec

English

MD_1969443-2_09062018852_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English