206036-2 ✔ ACTIVE

AMP | AMP CPC

TE Internal #: 206036-2

Circular Power Connectors, Housing, 600 VDC, Wire-to-Panel, 3 Position, Wire & Cable, Receptacle, Pin, Power, Black, All Plastic, PA 6.6 GF, AMP CPC

View on TE.com >

Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC SERIES 3

Connector Product Type: **Housing**

Operating Voltage: **600 VDC**

Connector System: **Wire-to-Panel**

Number of Positions: **3**

Sealable: **No**

All CPC SERIES 3 (16)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	3
Number of Power Positions	3
Keying	A
Number of Signal Positions	0

Electrical Characteristics

Operating Voltage	600 VAC

Contact Features

Reverse Gender	No
Contact Type	Pin
Contact Current Rating (Max)	34 A
Contact Protection	With

Termination Features

Termination Method to Wire & Cable	Crimp

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Screw & Hole Thread Size	15/16-20 UNEF – 2A
Connector Mounting Type	Panel Mount
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	Without
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	PA 6.6 GF
Circular Connector Shell Size	17

Dimensions

Accepts Wire Insulation Diameter Range	5.59 mm[.22 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Power
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
VDE Tested	No

Packaging Features

Packaging Method	Standard
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 207299-3
FLANGE PLUG MOUNT CPC

TE Part # 206037-2
CPC PLUG ASSEMBLY SIZE 17-3

TE Part # 206037-1
CPC PLUG ASSEMBLY SIZE 17-16

TE Part # CAT-AM71-C83998B
CPC Cable Clamps

TE Part # 213810-1
CPC COUPLING RING SIZE 17

TE Part # 7-1579008-6
UNLOCKING TOOL



TE Part # 206037-3
CPC PLUG ASSEMBLY SZ 17-16



TE Part # 206037-4
CPC PLUG ASSEMBLY SZ 17-16

TE Part # 207241-1
CABLE BOOT,SZ 17,CPC

TE Part # 207387-1
CABLE GRIP,SZ 17,CPC



TE Part # 207387-2
CABLE GRIP,SZ 17,CPC

TE Part # 207597-1
PLUG, TYPE XII KEYING



TE Part # 4-2407269-1
CAP, CPC, SIZE 17 RECP, ORANGE

TE Part # 4-2407269-4
CAP, CPC, SIZE 17 RECP, YELLOW

TE Part # 4-2407269-3
CAP, CPC, SIZE 17 RECP, RED

TE Part # 4-2407269-2
CAP, CPC, SIZE 17 RECP, BLACK

Also in the Series | AMP CPC

Circular Connector Adapters(7)

Circular Connector Boots & Strain Relief(6)

Circular Connector Caps & Covers(16)

Circular Connector Hardware(3)

Circular Connector Keying Plugs(2)

Circular Connector Seals(36)

Circular Power Connectors(467)

Insertion & Extraction Tools(1)



Power Contacts(6)

Sealing Sleeves(2)

Unscreened Circular Connector Backshells & Clamps(56)

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_206036-2_AZ.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_206036-2_AZ.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_206036-2_AZ.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Connector, Circular Plastic

English

Product Specification

English

Product Specification

English

Product Environmental Compliance

MD_206036-2_0409201408_dmtec

English

MD_206036-2_0409201408_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English