
MODULINK™ 880MP SERIES FLOOR BOXES


Modulink 880MP Series Floor Boxes Metal Cover Plates Ordering Information (continued0

829CK Brass Communications Cover Plate




2 5/8" and 2 1/4" (67mm and 57mm) plugs. Not for use with threaded conduit.

829CK-1/2 Brass Communications Cover Plate




Brass communications cover plate, 2 5/8" and 1/2" (67mm and 12.7mm) plugs. For carpet or tile installations. Not for use with threaded conduit.

829CK-1 Brass Communications Cover Plate




2 5/8" and 1" (67mm and 25mm) plugs. Not for use with threaded conduit.

828MAAP A/V Adapter Plate



Sheet metal adapter plate that accepts two (2) Legrand AVIP or Extron Electronics MAAP style device plates, sold separately. For use with 828GFITC or 828GFITCAL cover plates, sold separately.

829CK-3/4 Brass Communications Cover Plate




2 5/8" and 3/4" (67mm and 19.1mm) plugs. Not for use with threaded conduit.

NOTE: Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.


Modulink 880MP Series Floor Boxes Brushed Aluminum Cover Plate Flanges Ordering Information

818TCAL One-Gang Brushed Aluminum Combination Carpet and Tile Flange




Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

838TCAL Three-Gang Brushed Aluminum Combination Carpet and Tile Flange



Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

828TCAL Two-Gang Brushed Aluminum Combination Carpet and Tile Flange




Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

NOTE: Brushed aluminum flanges come with beveled edges.

OMNIBOX™ SERIES FLOOR BOXES


Omnibox Series Metal Cover Plates Ordering Information (continued)

828DPGFITC Brass Rectangular Cover Plate



Allows for mounting of a duplex style receptacle with a rectangular style flip lid cover.


828COMTC Brass Communications Cover Plate



Allows for up to four communication devices to be mounted in a recessed position within the 880 Floor Box. The 828COM Cover Plates has removable slides for cable egress.


NOTE: For use with 880S and 880CS Series Boxes only.

828DLR Brass Single Locking Receptacle Cover Plate




Single flip lid cover for 20A or 30A single locking receptacles. Device opening is 2 5/8" (67mm). For use with maximum female locking device of 1.58" diameter and maximum male plug face of 2.25" diameter.

828SPTC Brass Duplex Cover Plate




Screw plugs. Screw plugs are 1 1/2" (38mm) in diameter.

829STC Brass Communication Cover Plate




Data slides. Feed through only, not for use with a mounting plate for communication adapter.

829CK Brass Communication Cover Plate




2 5/8" and 2 1/4" (67mm and 57mm) plugs.

829CK-1 Brass Communications Cover Plate




2 5/8" and 1" (67mm and 25mm) plugs.

829CK-3/4 Brass Communications Cover Plate




2 5/8" and 3/4" (67mm and 19.1mm) plugs.

829CK-1/2 Brass Communications Cover Plate



2 5/8" and 1/2" (67mm and 12.7mm) plugs.

828MAAP A/V Adapter Plate



Sheet metal adapter plate that accepts two (2) Legrand AVIP or Extron Electronics MAAP style device plates, sold separately. For use with 828GFITC or 828GFITCAL cover plates, sold separately.


NOTE: UL Listed for tile, terrazzo and carpet floors.

Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.

880W SERIES™ FLOOR BOXES


880W Series Floor Boxes Metal Cover Plates Ordering Information (continued)

828DPGFITC Brass Rectangular Cover Plate




Allows for mounting of a duplex style receptacle with a rectangular style flip lid cover.

828DLR Brass Single Locking Receptacle Cover Plate




Single flip lid cover for 20A or 30A single locking receptacles. Device opening is 2 5/8" (67mm). For use with maximum female locking device of 1.58" diameter and maximum male plug face of 2.25" diameter.

828SPTC Brass Duplex Cover Plate




Screw plugs are 1 1/2" (38mm) in diameter.

829STC Brass Communication Cover Plate



Data slides. Feed through only, not for use with a mounting plate for flush mounted communication adapter.


829CK Brass Communication Cover Plate



2 5/8" and 2 1/4" (67mm and 57mm) plugs.


NOTE: UL Listed for tile, terrazzo and carpet floors.Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.

829CK-1/2 Brass Communication Cover Plate




2 5/8" and 1/2" (67mm and 12.7mm) plugs. For carpet or tile installations.

829CK-3/4 Brass Communication Cover Plate




2 5/8" and 3/4" (67mm and 19.1mm) plugs.

829CK-1 Brass Communication Cover Plate




2 5/8" and 1" (67mm and 25mm) plugs.

828MAAP A/V Adapter Plate



Sheet metal adapter plate that accepts two (2) Legrand AVIP or Extron Electronics MAAP style device plates, sold separately. For use with 828GFITC or 828GFITCAL cover plates, sold separately.

828COMTC Brass Communication Cover Plate



Allows for up to four communication devices to be mounted in a recessed position within the 880 Floor Box. The 828COM Cover Plate has removable slides for cable egress.


NOTE: For use with 880S and 880CS Series Boxes only.

FIRE CLASSIFIED FLOOR BOXES

Omnibox™ Series Floor Boxes


OmniBox Series Floor Boxes Metal Cover Plates Ordering Information

828R Brass Duplex Cover Plate




Flip lids. Can also be used with a 106 type communication adapter.

828GFITC Brass GFI Cover Plate




May be used with Activate and Ortronics® Connectivity Systems in conjunction with 817B, 827B and 837B Flanges.

828DPGFITC Brass Rectangular Cover Plate



Allows for mounting of a duplex-style receptacle with a rectangular-style flip lid cover.


828COMTC Brass Communication Cover Plate



Allows for up to four communication devices to be mounted in a recessed position within the 880 Floor Box. The 828COM Cover Plate has removable slides for cable egress.


NOTE: For use with 880S and 880CS Series Boxes only.

828DLR Brass Single Locking Receptacle Cover Plate




Single flip lid cover for 20A or 30A single locking receptacles. Device opening is 2 5/8" (67mm). For use with maximum female locking device of 1.58" diameter and maximum male plug face of 2.25" diameter.

828SPTC Brass Duplex Cover Plate




Screw plugs. Screw plugs are 1 1/2" (38mm) in diameter.

829STC Brass Communication Cover Plate




Data slides. Feed through only, not for use with a mounting plate for communication jacks.

829CK Brass Communication Cover Plate




2 5/8" and 2 1/4" (67mm and 57mm) plugs.

829CK-1 Brass Communication Cover Plate




2 5/8" and 1" (67mm and 25mm) plugs.

829CK-3/4 Brass Communication Cover Plate




2 5/8" and 3/4" (67mm and 19.1mm) plugs.

829CK-1/2 Brass Communication Cover Plate



2 5/8" and 1/2" (67mm and 12.7mm) plugs.

828MAAP A/V Adapter Plate



Sheet metal adapter plate that accepts two (2) Legrand AVIP or Extron Electronics MAAP style device plates, sold separately. For use with 828GFITC or 828GFITCAL cover plates, sold separately.

NOTE: UL Listed for terrazzo, polished concrete, wood, tile and carpet covered concrete floors.

Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.