

Step 1 (Cont.)

Select Feeders

CIRCUIT BREAKERS	UL LISTED KAIC		SIZE	CAT#
	240VAC	480VAC		
Spectra RMS SED 3P 600V 30A	18	18	3X	EZSEDA36AT0030
Spectra RMS SEH 3P 600V 30A	65	25	3X	EZSEHA36AT0030
Spectra RMS SEL 3P 600V 30A	100	65	3X	EZSELA36AT0030
Spectra RMS SEP 3P 600V 30A	200	100	3X	EZSEPA36AT0030
Spectra RMS SED 3P 600V 60A	18	18	3X	EZSEDA36AT0060
Spectra RMS SEH 3P 600V 60A	65	25	3X	EZSEHA36AT0060
Spectra RMS SEL 3P 600V 60A	100	65	3X	EZSELA36AT0060
Spectra RMS SEP 3P 600V 60A	200	100	3X	EZSEPA36AT0060
Spectra RMS SED 3P 600V 100A	18	18	3X	EZSEDA36AT0100
Spectra RMS SEH 3P 600V 100A	65	25	3X	EZSEHA36AT0100
Spectra RMS SEL 3P 600V 100A	100	65	3X	EZSELA36AT0100
Spectra RMS SEP 3P 600V 100A	200	100	3X	EZSEPA36AT0100
Spectra RMS SED 3P 600V 150A	18	18	3X	EZSEDA36AT0150
Spectra RMS SEH 3P 600V 150A	65	25	3X	EZSEHA36AT0150
Spectra RMS SEL 3P 600V 150A	100	65	3X	EZSELA36AT0150
Spectra RMS SEP 3P 600V 150A	200	100	3X	EZSEPA36AT0150
Spectra RMS SFH 3P 600V 250A	65	35	3X	EZSFHA36AT0250
Spectra RMS SFL 3P 600V 250A	100	65	3X	EZSFLA36AT0250
Spectra RMS SFP 3P 600V 250A	200	100	3X	EZSFPA36AT0250
Spectra RMS SGH 3P 600V 400A	65	35	4X	EZSGHA36AT0400
Spectra RMS SGHH 3P 600V 400A 100% Rated	65	35	4X	EZSGHH36AT0400
Spectra RMS SGL 3P 600V 400A	100	65	4X	EZSGLA36AT0400
Spectra RMS SGLL 3P 600V 400A 100% Rated	100	65	4X	EZSGLL36AT0400
Spectra RMS SGP 3P 600V 400A	200	100	4X	EZSGPA36AT0400
Spectra RMS SGP 3P 600V 400A 100% Rated	200	100	4X	EZSGPP36AT0400
Spectra RMS SGH 3P 600V 600A	65	35	4X	EZSGHA36AT0600
Spectra RMS SGL 3P 600V 600A	100	65	4X	EZSGLA36AT0600
Spectra RMS SGP 3P 600V 600A	200	100	4X	EZSGPA36AT0600
Spectra RMS SKH 3P 600V 800A	65	50	6X	EZSKHA36AT0800
Spectra RMS SKL 3P 600V 800A	100	65	6X	EZSKLA36AT0800