



P65

Technical Data



Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	26.30 x 10.91 x 11.38
Case Weight (lbs)	17.64
Country of Origin	Malaysia
Lens	Mirror
Frame Style	Rimless
Lens Color	Silver
Frame Fit	Universal
Lens Coating	Anti-Scratch
Product Circularity	Recycled via Terracycle

Bouton® Optical Wilco™

Rimless Safety Glasses with Black Temple, Silver Mirror Lens and Anti-Scratch Coating

- Lightweight, rimless design provides all day user comfort
- Adjustable length temples provide a secure, accurate fit
- Ribbed rubber nosepiece for maximum comfort and fit
- 7 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Drivers
- Marine
- Drilling Rig

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-04

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-92-0000	Black	Clear	Clear	AS	616314131462	01616314131461	02616314131460
250-92-0001	Black	Tinted	Gray	AS	616314131479	01616314131478	02616314131477
250-92-0002	Black	I/O	Clear	AS	616314131486	01616314131485	02616314131484
250-92-0005	Black	Mirror	Silver	AS	616314161940	01616314161949	02616314161948
250-92-0009	Black	Tinted	Amber	AS	616314131493	01616314131492	02616314131491
250-92-0020	Black	Clear	Clear	AS/AF	616314131509	01616314131508	02616314131507
250-92-0021	Black	Tinted	Gray	AS/AF	616314161957	01616314161956	02616314161955

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated