PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : CH135 Cholesterol, NF

CAS# : 57-88-5

Formula : C27H46O

Formula Weight : 386.65

Test	Limit Min.	Max.
SOLUBILITY IN ALCOHOL	TO PASS TEST	
MELTING RANGE	147°-150°C	
SPECIFIC ROTATION	-34° TO -38°	
ACIDITY	TO PASS TEST	
LOSS ON DRYING	--	0.3%
RESIDUE ON IGNITION	--	0.1%
IDENTIFICATION	TO PASS TEST	
RETEST DATE		
RESIDUAL SOLVENTS:	TO PASS TEST	